

Product data sheet

Characteristics

QOGP3P3036P

Generator panel, QO, 1 phase, 18 spaces, 36 circuits, 30A main breaker, PoN, NEMA1, cover with door, UL



Main

Marketing Trade Name	QO
Product	Panel

Complementary

Tightening torque	Cover 20 lb.in
Load Center Type	Main Breaker
[In] rated current	30 A
Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	36
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Grounding Bar	Grounding bar (ordered separately)
Height	17.91 in (455 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient air temperature for operation	23 °F (-5 °C) 104 °F (40 °C)
Product certifications	UL listed

Packing Units

Package 1 Weight	20.50 lb(US) (9.299 kg)
------------------	-------------------------