

Product data sheet

Characteristics

QON330L200

OEM MTG BASE QO MLO 240V 200A 3PH 30SP

Product availability : Stock - Normally stocked in distribution facility

Price* : 477.00 USD



Main

Range of product	QO
------------------	----

Complementary

[Ue] rated operational voltage	208Y/120 V AC 240 V AC
AWG gauge	AWG 4...300 kcmil aluminium/copper
Maximum Depth	1.013 in (25.73 mm)
Maximum Height	5.03 in (127.76 mm)
Phase	3 phase
Number of spaces	30
Short-circuit protection	10 kA
Product compatibility	QO circuit-breaker
Product destination	QO circuit breaker QO-GFI circuit breaker QO-EPD circuit breaker
Maximum Width	7.514 in (190.86 mm)
Wiring configuration	3-wire

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	00909 - MOUNTING BASES, S/N
Discount Schedule	DE3A
GTIN	00785901868279
Nbr. of units in pkg.	1
Package weight(Lbs)	3.78 lb(US) (1.71 kg)
Returnability	Yes
Country of origin	US

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Oct 9, 2020

Packing Units

Package 1 Height	4.10 in (10.414 cm)
Package 1 width	13.00 in (33.020 cm)
Package 1 Length	21.00 in (53.340 cm)

Offer Sustainability

RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------