

Product data sheet

Characteristics

QOU125

QOU Miniature Circuit Breaker, 25A, 1P,
120/240V, 10kA

Product availability : Stock - Normally stocked in distribution facility



Price* : 40.20 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QOU
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated

Complementary

Line Rated Current	25 A
Number of Poles	1P
Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC 5 kA 48 V DC
Electrical connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] rated operational voltage	120/240 V AC 120 V AC 48 V DC
Mounting mode	Unit mount
AWG gauge	AWG 14...AWG 2 aluminium/copper
Maximum Height	4.05 in (102.87 mm)
Depth	2.95 in (74.93 mm)
Width	0.75 in (19.05 mm)
Tightening torque	45 lbf.in (5.08 N.m) AWG 14...AWG 2)

Environment

Product certifications	UL Listed IEC
------------------------	------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00900 - QOU BREAKERS & SWITCH
Discount Schedule	DE2
GTIN	00785901489085
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35 lb(US) (0.16 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	0.90 in (2.286 cm)
Package 1 width	3.10 in (7.874 cm)
Package 1 Length	4.50 in (11.430 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------