

Product data sheet

Characteristics

QOU215H5283

QOU Miniature Circuit Breaker, 15A, 2P, 240V, 10kA, Ring Terminal

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 252.00 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QOU
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated

Complementary

Line Rated Current	15 A
Number of Poles	2P
Interrupt Rating	10 kA at: 240 V AC
Electrical connection	Ring tongue, line side Ring tongue, load side
System Voltage	240 V AC
Mounting mode	Unit mount
AWG gauge	AWG 14...AWG 2 (aluminium/copper)
Height	4.05 in
Depth	2.95 in
Width	1.5 in

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	00900 - QOU BREAKERS & SWITCH
Discount Schedule	DE2

Nbr. of units in pkg.	1
Package weight(Lbs)	0.35000000000000003
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1424 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------