

# Product data sheet

## Characteristics

# QOU215VH5283

QOU Miniature Circuit Breaker, 15A, 2P,  
120/240V, 22kA, Ring Terminal

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 243.00 USD



### Main

Product or component type	Miniature circuit-breaker
Range of product	QOU
Circuit breaker type	Standard

### Complementary

Line Rated Current	15 A
Number of Poles	2P
Interrupt Rating	22 kA at: 120/240 V AC
Electrical connection	Ring tongue, line side Ring tongue, load side
System Voltage	120/240 V AC
Mounting mode	Unit mount
AWG gauge	AWG 14...AWG 2 (aluminium/copper)
Height	4.05 in
Depth	2.95 in
Width	1.5 in

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

### Ordering and shipping details

Category	00900 - QOU BREAKERS & SWITCH
Discount Schedule	DE2
GTIN	00785901333609

Nbr. of units in pkg.	1
Package weight(Lbs)	0.75
Returnability	N
Country of origin	MX

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------