

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Surge protection device
---------	-------------------------

### Complementary

Surge Current	40 kA
System Voltage	480Y/277 V AC
Phase	3 phases
Wiring Configuration	4-wire
Connection	Wire AWG 12 copper
MCOV	180 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED = normal operation
Mounting Support	Panel mounting
Height	3.07 in (78 mm)
Width	3.62 in (92 mm)
Depth	2.64 in (67 mm)

### Environment


Enclosure Rating	NEMA 4X
Enclosure Material	Plastic, colour : black
Standards	CSA C22.2 No 8 1986 UL 1449 ed. 4
Ambient Operating	149 °F (65 °C)

### Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
----------	-------------------------------

Discount Schedule	DE1B
GTIN	00785901558200
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	Y
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1640 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	DINP which is known to the State of California to cause cancer and
- - - - - Substance 2	DIDP which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>