



Main

Range of product	Modicon M171/M172
Product or component type	Display module
Supply	External source

Complementary

Display type	LCD display Colour touchscreen
Display resolution	320 x 240 pixels
Colour	White
[Us] rated supply voltage	24 V AC/DC
Power consumption in W	3.2 VA 1.3 W
Analogue input type	NTC 10k type 2 temperature probe - 40...50 °C +/- 0.1 °C NTC 10k temperature probe at 21 °C +/- 0.5 °C
Product compatibility	Logic controller M171 Logic controller M172
Height	120 mm
Width	86 mm
Depth	25 mm
Net weight	0.34 kg

Environment

Directives	1907/2006/EC - REACH directive 2011/65/EU - RoHS directive 2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	EN 60950-1 EN 55024 EN 55032 UL 873

Product certifications	RCM EAC CE CTUVus
Ambient air temperature for operation	0...50 °C
Ambient air temperature for storage	-30...50 °C

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins