

Product data sheet

Characteristics

VLSH2H5R

TeSys VLS - rot. handle - holefixing - red - shaft 5 mm - 65x65 mm

Product availability : Stock - Normally stocked in distribution facility

Price* : 23.97 USD



Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks, with diameter 4...8 mm
Marking	0 - 1

Complementary

Fixing mode	Hole, with diameter 22.5 mm
Tightening torque	20.35 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 in (65 mm)
Width	2.56 in (65 mm)
Depth	2.85 in (72.5 mm)
Product weight	0.15 lb(US) (0.068 kg)

Environment

IP degree of protection	IP65
NEMA degree of protection	NEMA 2 for use with device conforming to UL 508 NEMA 3R for use with device conforming to UL 508 NEMA 4 for use with device conforming to UL 508 NEMA 4X for use with device conforming to UL 508 NEMA 12 for use with device conforming to UL 508 NEMA 12K for use with device conforming to UL 508 NEMA 1

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1

GTIN	00785901575948
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14000000000000001
Returnability	Y
Country of origin	IT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1441 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---