



Main

Range of product	Acti 9
Product name	Acti 9 iPB
Product or component type	Push-button
Device short name	IPB
Standards	IEC 60669-1 IEC 60947-5-1

Complementary

Contacts type and composition	1 NC
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	1 push-button red
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside : Libro Upside : ProDis Upside : Clario
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22 : 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal 1 cable(s) 0.5 mm ² rigid Staggered tunnel terminal 1 cable(s) 0.5 mm ² flexible Staggered tunnel terminal 1 cable(s) 0.5 mm ² flexible with ferrule Staggered tunnel terminal 2 cable(s) 2.5 mm ² rigid Staggered tunnel terminal 2 cable(s) 2.5 mm ² flexible Staggered tunnel terminal 2 cable(s) 2.5 mm ² flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Tropicalisation	2
Relative humidity	95 % (55 °C)
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------