PRESSURE

ROOM CONDITION MONITOR

SRCM SERIES

DESCRIPTION

The **Setra SRCM Series** is a 2-in-1 solution incorporating the best of the **SRPM** and adding room condition monitoring capability. A large 4.3" TFT displays room conditions such as room ID, room pressure mode, room status, room pressure and a slide bar that indicates pressure relative to set point. It is also capable of displaying a full screen room condition banner to communicate the current room status and is easily programmed through the SmarTTouch $^{\text{TM}}$ display

The **SRCM Series** incorporates a flush mount design for the most esthetic installation. The display hinges up for easy access to a USB port that is provided for quick cloning of multiple units. The **SRCM Series** also has Multi-room dP measurement capabilities with the use of a remote dP transmitter, as well as the ability to display up to eight parameters utilizing BACnet[®] MSTP. In addition to the standard analog and relay outputs, the **SRCM Series** is available in a BACnet[®] MSTP configuration that is easily setup through the SmarTTouch[™] display.

The **SRCM Series** is perfect for applications in laboratory, pharmaceutical, research, isolation room, and surgical suite applications or anywhere maintaining and monitoring differential pressure.

FEATURES

- · Color coded room status indication
- Flush mount design
- · New intuitive interactive interface
- Clone configuration capability
- Selectable analog voltage and milliamp outputs









Optional Remote Annunciator

Setra's SRAN annunciator allows remote indication of room status at monitoring or nurses station. A GREEN LED indicates a normal room condition, a RED LED and audible alarm signal a breach in room pressure status.

- SPDT alarm relay
- 4.3" TFT LCD display
- Optional BACnet MSTP
- SPDT relay output
- · Analog current or voltage outputs

SPECIFICATIONS

Setpoint (SP)

Supply Voltage 18-32 VAC, 50-60HZ, 10VA

Signal Output (Volts, Current, Switch)

0 to (5,10) VDC or 4-20mA

Alarm SPDT, 0.6A @ 120VAC, 2A @ 30 VDC

Max Voltage Output Impedance
5KO

Min Current Output Impedance

510Ω

Digital Input Dry contact door switch

Analog Input Two 0-(5,10VDC) or 4-20mA inputs (for

opt. remote pressure sensors)
Adjust Local Alarm value set on

touch screen

Control Type Single room differential pressure

monitor

Communication (if any) BACnet MS/TP Field Interface Devices (order Separately)

RPS SS room pressure probe

Display/Audible (If any) Dimmable color touchscreen 4.3",

480 x 272,

4 color status indicators

0-4 Audible settings w/ silence switch

Accuracy $\pm 0.5\%$, $\pm 0.25\%$ optional

Resolution 0.0001" WC Sensor Type Capacitive

Normal Measurement Range

±0.05" to 5" WC

Overpressure (Burst) ± 27 " WC, (Units = 0.1"WC = ± 15 " WC)

Max Operating Pressure (Proof)

 ± 27 " WC, (Units = 0.1"WC = ± 15 " WC)

Operating Temperature 32° to 120°F (0° to 50°C)
Operating Humidity 5 to 95% RH (Non-condensing)
Wetted Parts Stainless steel, glass, silicone, brass,

steel

Media Compatibility Inert dry air

Process Connection Two-3/16" OD brass H/L,

for 1/4" OD tubing

Wiring Terminations
Mounting
Single Flush w/3 gang double deep box (7")
Single Flush w/4 gang double deep box (7")
Single Flush w/4 gang double deep box (

Dimensions 7.45"W x 5.84"H x 0.38"D,

(18.9 x 14.8 x 0.97 cm)


Weight 1.2 lb (0.55 kg)
Approvals UL, CE, CSA, RoHS

Warranty 1 year



ROOM CONDITION MONITOR SRCM SERIES





ORDERING INFORMATION

MODEL	DESCRIPTION						
SRCM	Room pressure and condition monitor						
	PRESSURE RANGES						
	R05WB +/-0.05"WC						
	0R1WB	0R1WB +/-0.10"WC					
	R25WB	R25WB +/-0.25"WC					
	0R5WB	OR5WB +/-0.50"WC					
	001WB	+/-1.00"WC					
	2R5WB	WB +/-2.50"WC					
	005WB +/-5.00"WC						
	025LB	025LB +/-25 Pa					
	050LB						
	100LB						
	250LB	+/-250 Pa					
	500LB	+/-500 Pa					
	10CLB		+/-1000 Pa				
			SUPPLY VOLTAGE				
		A1			20 mA, 0-5 VDC or 0-10 VDC		
		A2	2 : 17 :0 :11::: 27 :0:::01				
			ACCURACY				
			<u>H</u>	.,	0.5% full scale		
			F		0.25% full scale		
					SSURE SNUBBER		
				N	No snubber		
				1	One snubber		
				2	Two snubbers		

RELATED PRODUCTS

RPS Stainless steel room pressure sensor, 1/4" barb lvory plastic room pressure sensor, 1/4" barb RPS-W White plastic room pressure sensor, 1/4" barb 1/4" 0D black poly tubing, 1 coil, 250 ft (76 m)

SRAN Remote annunciator with red and green status LEDs, audible alarm and acknowledge switch