

# Product data sheet

Specifications



## APC Smart-UPS Ultra, 3000VA 120V 1U, with Lithium-Ion Battery, with Network Management Card Embedded

SRTL3KRM1UNC

### Main

Main Input Voltage	120 V 125 V
Other Input Voltage	120 V 125 V
Main Output Voltage	120 V
Other Output Voltage	120 V 125 V
Rated power in W	2880 W
Rated power in VA	2880 VA
Input Connection Type	NEMA L5-30P
Output connection type	5 NEMA 5-20R 1 NEMA L5-30R
Number of rack unit	1U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery type	Li-Ion (Lithium-Ion)
Provided equipment	RJ45 cable USB cable Country-specific detachable power cord Rack mounting brackets Rack mounting support rails Installation guide Warranty card

### General

Redundant	No
-----------	----

### Physical

Colour	Silver grey
Height	1.69 in (43 mm)
Width	17.01 in (432 mm)
Depth	22.05 in (560 mm)
Net weight	35.05 lb(US) (15.9 kg)
Mounting preference	No preference
Mounting mode	Rack-mounted with kit Tower-mounted with kit

Two post mountable	1
USB compatible	Yes
<b>Input</b>	
Network frequency	50/60 Hz
<b>Output</b>	
Maximum configurable power in W	2880 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
UPS type	On-Line
Wave type	Sine wave
Bypass type	Internal bypass (automatic and manual)
Maximum configurable power in VA	2880 VA
<b>Conformance</b>	
Product certifications	UL/cUL listed FCC
Standards	UL 1778 CSA C22.2 No 107.3-05 FCC part 15 class A
<b>Environmental</b>	
Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	55 dB
IP degree of protection	IP20
<b>Batteries &amp; Runtime</b>	
Battery recharge time	1.5 h
Battery voltage	50 V
Battery charger power	448 W
Battery power in VAH	312 VAh runtime
Battery option	SRTL50RMBP1U-LI 1 1452 VAh SRTL50RMBP1U-LI 2 2592 VAh SRTL50RMBP1U-LI 3 3732 VAh SRTL50RMBP1U-LI 4 4872 VAh SRTL50RMBP1U-LI 5 6012 VAh
Extended runtime	1
<b>Communications &amp; Management</b>	
Control panel	Multifunction LCD status and control console

Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes
Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.95 in (278.2 mm)
Package 1 Width	22.20 in (564 mm)
Package 1 Length	30.08 in (764 mm)
Package 1 Weight	53.3 lb(US) (24.18 kg)
Offer Sustainability	
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Contractual warranty	
Warranty	5 years repair or replace
Recommended replacement(s)	