

ALARMS AND INDICATION



WALL-MOUNTED STROBES MODELS STB, STB-H

DESCRIPTION

Models **STB** and **STB-H Wall-Mounted Strobes** provide a bright, eye-catching warning light for any alarm application. The **Model STB-H** features a distinct audible signal.

SPECIFICATIONS

Power	20-31 VDC (24 VDC nominal)
Strobe frequency	1 Hz
Strobe intensity	15 (off-center) candela 75 (on-center) candela
Current	
Strobe	190 mA max
Horn	37 mA max
Horn intensity	104 dB max
Connections	Terminal blocks
Operating temp	32° to 120°F (0° to 49°C)
Approvals	UL listed
Dimensions	4.5"H x 4.56"W x 2.25"D (11.43 x 11.58 x 5.72 cm)
Warranty	3 years



STB

STB-H



3

ORDERING INFORMATION

MODEL	DESCRIPTION
STB	Wall-mounted strobe
STB-H	Wall-mounted strobe with horn

ALARM HORN SC SERIES

DESCRIPTION

SC Series Alarm Horns provide an audible tone when an electric signal is applied. They can be used in applications when an audible alarm is needed to indicate that immediate attention is required.

SPECIFICATIONS

Power	
SC628	6-28 VDC
SC628A, AN	6-28 VAC/VDC
SC110	30-120 VAC/VDC
Tone	Continuous
Mounting	Panel, cutout 1.13" (2.87 cm)
Loudness	Medium, 68-80 dB (AN model Loud, 80-95 dB)
Current	
SC628	3-18 mA
SC628A	6-23 mA
SC628AN	4-30 mA
SC110	6-21 mA
Approvals	UL-recognized component, File #S1290
Warranty	1 year



ORDERING INFORMATION

MODEL	DESCRIPTION
SC628	Alarm horn, 24 VDC
SC628A, AN	Alarm horn, 24 VAC/VDC
SC110	Alarm horn, 120 VAC

PULSE OR RUN-TIME ACCUMULATOR DISPLAY MODEL ALD-1

DESCRIPTION

The **Model ALD-1** is a 5-1/2 digit LCD resettable accumulator or run-time counter. The lithium battery provides years of trouble-free service. Two wires are all that are necessary to totalize consumption, flow data, or run-time data. No external power supply is necessary.



ALD-1C

ALD-1

SPECIFICATIONS

Display	5-1/2 digit	Battery life	10 years nominal
Digit size	0.2" (0.51 cm) high	Range	0-199999
Count speed	Accumulator 100 counts per second Timer counts in one-hour or 0.1-hour increments	Dimensions	
Input	Contact or solid-state switch	Bezel	1.1"H x 2.09"W x 1.72"D (2.79 x 5.3 x 4.37 cm)
Reset	Push button or remote contact	Panel cutout	1.0"H x 2.0"W (2.54 x 5.08 cm)
Operating temp	32° to 122°F (0° to 50°C)	Weight	2.1 oz (59.5 g)
		Warranty	2 years

ORDERING INFORMATION

MODEL	DESCRIPTION
ALD-1	LCD push-button resettable accumulator counter
ALD-1R	LCD remote reset accumulator counter
ALD-10C	LCD run-time remote reset clock, one-hour increments
ALD-1C	LCD run-time remote reset clock, 0.1-hour increments