

THERMOSTATS & CONTROLLERS

THERMOSTAT ACCESSORIES

TE6001, CC-1G, M645K, 356-90K, M-2500, APB-28, PN-46, WALL PLATE ADAPTERS



DESCRIPTION

Models **TE6001, CG-1G, M645K, 356-90K, M-2500, APB-28, and PN-46** are all sensor mounting brackets for averaging, duct, and outside air probe applications. They have a 1/4" clip or guide to firmly hold a temperature sensor for the application.

TE6001-1 Duct temperature element holder with box



TE6001-8 Duct temperature element holder without box



M-648K Copper-clad capillary mounting clip



CC-1G Plastic capillary and sensor holder mounting clip



APB-28 Adjustable pipe bracket 2"-8" diameter



PN-46 Aluminum sensor holder with adhesive backing



DESCRIPTION

Wall adaptor plates (goof plates) offer concealment of plaster irregularities, and are ideal to cover up old thermostat mounting holes or paint ridges. Foam backing pads offer wall insulation for better temperature readings. Switch plate displays offer readouts for temperature at every light switch.

10-531 White adaptor plate 7" x 5.25" (KTR,KHR)



50002883-001 White wall plate 6" x 8.3" (TH5000, TH6000)



65345 White wall adaptor plate 4" x 4" (PECO)



BA/ADP-525-7-WMW Warm white adaptor plate 7" x 5.25"

BA/ADP-525-7-OFW Off white adaptor plate 7" x 5.25"

BA/ADP-525-7-CPW Copla white adaptor plate 7" x 5.25"

BA/FOAMBACK White foam back insulator, 4.4" x 2.6"

BA/FOAMBACK-GREY Grey foam back insulator, 4.4" x 2.6"

