

## Rack ATS, 100/120V, 15A, 5-15 in, (10) 5-15R out

### AP4450

Call for More Information +61 2 9125 8951



- Includes: Mounting hardware, Rack mounting brackets, Serial configuration cable

#### Output

Nominal Output Voltage	100V, 120V
Maximum Total Current Draw	15
Output Connections	(10) NEMA 5-15R

#### Input

Nominal Input Voltage	100V, 120V
Input frequency	50/60 Hz
Input Connections	NEMA 5-15P
Cord Length	2.4meters
Number of Power Cords	2
Load Capacity	1440VA
Maximum Input Current	15A
Regulatory Derated Input Current (North America)	12A

#### Physical

Maximum Height	44MM, 4.4CM
Maximum Width	432MM, 43.2CM
Maximum Depth	236MM, 23.6CM
Rack Height	1U
Net Weight	4.4KG
Shipping weight	6.17KG

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Physical	
Shipping Height	114MM, 11.4CM
Shipping Width	600MM, 60.0CM
Shipping Depth	356MM, 35.6CM
Color	Black

Environmental	
Operating Temperature	-5 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-25 - 65 °C
Storage Elevation	0 - 15240meters

Conformance	
Approvals	FCC part 15 class A, ICES-003, PSE, TÜV-C, TÜV-NURTL, VCCI class A
Standard warranty	2 years repair or replace