

Technical Specifications

APC NetShelter SX 12U Server Rack Enclosure 600mm x 900mm w/ Sides Black | AR3003 | Downloaded on 06/01/2020 (EST)



APC NetShelter SX 12U Server Rack Enclosure 600mm x 900mm w/ Sides Black

New

AR3003

Call for More Information

- Feature-rich rack enclosure optimized for easy installation, managing cables, integrating power distribution, and maximizing airflow.
- Includes: Casters, Doors, Key(s), Leveling feet, Roof, Side panels

Physical	
Maximum Height	658MM, 65.8CM
Maximum Width	600MM, 60.0CM
Maximum Depth	900MM, 90.0CM
Rack Height	12U
Net Weight	53.98KG
Shipping weight	75.0KG
Shipping Height	795MM, 79.5CM
Shipping Width	750MM, 75.0CM
Shipping Depth	995MM, 99.5CM
Color	Black
Maximum Mounting Depth	756.0MM, 75.57CM
Minimum Mounting Depth	191.0MM, 19.1CM
Front Door	16.0gauge
Vertical Posts	16.0gauge
Rear Door	18.0gauge
Roof	18.0gauge
Side Panels	18.0gauge
Units per Pallet	1.0
Rack Width	19"
Weight Capacity (static load)	272.73KG
Weight Capacity (dynamic load)	272.73KG

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

APC NetShelter SX 12U Server Rack Enclosure 600mm x 900mm w/ Sides Black | AR3003 | Downloaded on 06/01/2020 (EST)



Environmental	
Protection Class	IP 20
Conformance	
Approvals	UL 2416, UL 60950-1
Standard warranty	5 year repair or replace

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.