



NetShelter WX Fan Module

AR8213

In Stock
\$99.99*

- Air distribution systems for power dense racks and low pressure areas

Input	
Nominal Input Voltage	115V
Input frequency	60 Hz
Input Connections	IEC-320 C14
Number of Power Cords	1

Physical	
Maximum Height	1.7inches (43MM, 4.3CM)
Maximum Width	19.0inches (483MM, 48.3CM)
Maximum Depth	5.2inches (132MM, 13.2CM)
Net Weight	5.95lbs. (2.7KG)
Shipping weight	6.6lbs. (2.99KG)
Shipping Height	4.66inches (118MM, 11.8CM)
Shipping Width	22.8inches (579MM, 57.9CM)
Shipping Depth	8.1inches (206MM, 20.6CM)
Color	Black

Conformance	
Approvals	UL 507
Standard warranty	2 year (manufacturer's defect)

Sustainable Offer Status	
RoHS	Compliant
REACH	REACH: Contains No SVHCs

*Prices are indicative
Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.