

## Technical Specifications

Back-UPS 850VA, 2 USB charging ports | BE850G2 | Downloaded on 07/31/2020 (EST)

Life Is On 



# Back-UPS 850VA, 2 USB charging ports

## BE850G2

Call for More Information 800-800-4272

- Battery Backup & Surge Protector for Electronics and Computers
- Includes: USB cable, User Manual

### Output

<b>Output power capacity</b>	450Watts / 850VA
<b>Max Configurable Power (Watts)</b>	450Watts / 850VA
<b>Nominal Output Voltage</b>	120V
<b>Output Frequency (sync to mains)</b>	50/60Hz +/- 3 Hz
<b>Topology</b>	Standby
<b>Waveform type</b>	Stepped approximation to a sinewave
<b>Output Connections</b>	(6) NEMA 5-15R (3) NEMA 5-15R
<b>Transfer Time</b>	6ms typical : 10ms maximum

### Input

<b>Nominal Input Voltage</b>	120V
<b>Input frequency</b>	50/60 Hz +/- 3 Hz (auto sensing)
<b>Input Connections</b>	NEMA 5-15P
<b>Cord Length</b>	5ft (1.52meters)
<b>Input voltage range for main operations</b>	92 - 139V
<b>Number of Power Cords</b>	1

### Batteries & Runtime

<b>Battery type</b>	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
<b>Typical recharge time</b>	8hour(s)
<b>Replacement Battery</b>	<a href="#">RBC17</a> 

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Back-UPS 850VA, 2 USB charging ports | BE850G2 | Downloaded on 07/31/2020 (EST)



### Batteries & Runtime

Expected Battery Life (years)	2 - 5
Battery Charge Power (Watts)	13Watts
Battery Volt-Amp-Hour Capacity	104
Runtime	View Runtime Graph (Available in Technical Tab on site) View Runtime Chart (Available in Technical Tab on site)
Efficiency	View Efficiency Graph (Available in Technical Tab on site)

### Communications & Management

Interface Port(s)	USB
Control panel	LED status display with On Line : On Battery : Replace Battery and Building Wiring Fault
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

### Surge Protection and Filtering

Surge energy rating	354Joules
---------------------	-----------

### Physical

Maximum Height	5.47inches (139MM, 13.9CM)
Maximum Width	12.87inches (327MM, 32.7CM)
Maximum Depth	4.13inches (105MM, 10.5CM)
Net Weight	9.04lbs. (4.1KG)
Shipping weight	9.7lbs. (4.4KG)
Shipping Height	7.72inches (196MM, 19.6CM)
Shipping Width	16.38inches (416MM, 41.6CM)
Shipping Depth	6.61inches (168MM, 16.8CM)
Color	Black
Master Carton Units	2.0
Master Carton Weight	21.61lbs. (9.8)
# of Layers per Pallet	16.0
Pallet Weight	912.71lbs.

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Back-UPS 850VA, 2 USB charging ports | BE850G2 | Downloaded on 07/31/2020 (EST)



### Environmental

Operating Temperature	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000ft (0-3000meters)
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	10 - 90 %
Storage Elevation	0-50000ft (0-15000meters)
<b>Audible noise at 1 meter from surface of unit</b> 45.0dBA	

### Conformance

Approvals	California (CEC) Battery Charger, CSA C22.2 NO. 107.3, cTUVus, FCC Part 15 Class B, UL 1778
Equipment protection policy	Lifetime : \$75000
Standard warranty	3 years repair or replace

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs
Proposition 65 Warning	Available in Documentation tab

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.