



Battery Module for Symmetra PX, Smart-UPS VT or Galaxy 3500

SYBT4

Call for More Information +1-5000-55

Output	
Battery Output Voltage	384 V

Input	
Number of Power Cords	1

Batteries & Runtime	
Battery type	Lead-acid battery
Battery mounting	Enclosed battery cartridge
Battery Placement	Internal battery
Battery blocks per string	4
Battery Design Life	5 - 8
Battery Volt-Amp-Hour Capacity	2765

Physical	
Maximum Height	159MM, 15.9CM
Maximum Width	432MM, 43.2CM
Maximum Depth	711MM, 71.1CM
Net Weight	90.91KG
Shipping weight	101.82KG
Shipping Height	457MM, 45.7CM
Shipping Width	610MM, 61.0CM
Shipping Depth	838MM, 83.8CM

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Battery Module for Symmetra PX, Smart-UPS VT or Galaxy 3500 | SYBT4 | Downloaded on 08/24/2020 (EST)

Physical

Color	Black
Units per Pallet	7.0

Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0 - 1015.9meters
Storage Temperature	-15 - 40 °C
Storage Elevation	0 - 15240meters

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOL	Available in Documentation tab

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.