

Product data sheet

Specifications

SQUARE D



Meter socket, ringless, 3 phase, 4 wire, 7 jaws, solid top, lever bypass, jaw release

UTH7300T

Product availability : Stock - Normally stocked in distribution facility

Price* : 830.00 USD

Main

Product or Component Type	Meter Socket
Meter socket type	Ringless
Hub type	A-L ACPL closing plate

Complementary

Meter socket rated current	320 A
Number of jaws	7 with jaw release
Bypass type	Lever bypass
Phase	3 phase
[Ue] rated operational voltage	600 V AC
Enclosure Material	Steel
Box number	10R
Electrical connection	Studs
Service feed location	OH
Wiring configuration	4-wire
Height	36.62 in (930.15 mm)
Width	15.00 in (381.00 mm)
Depth	5.68 in (144.27 mm)

Environment

Product Certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00039-METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	785901627838
Returnability	Yes
Country of origin	US

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.90 in (17.526 cm)
Package 1 Width	15.70 in (39.878 cm)
Package 1 Length	36.00 in (91.44 cm)
Package 1 Weight	37.01 lb(US) (16.788 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------