

PANEL FABRICATION

FUSES

FLM, FLQ, FNQ, GF, K235, 251 SERIES

DESCRIPTION

FLM, FLQ, FNQ series midget fuses are slow-acting fuses used with 6SC30 & 6SM30 Series, 6M30 Series, 6W30 Series, and FB2X Series fuse holders. The **KLK-3** series fuses are fast-acting fuses.

SPECIFICATIONS/ORDERING INFORMATION					
AMP RATING	250V MODEL	500V MODEL	600V MODEL		
0.5	FLM-0.5	FLQ-0.5	FNQ-R-0.5		
0.8	FLM-0.8	FLQ-0.8	FNQ-R-0.8		
1.0	FLM-1	FLQ-1	FNQ-R-1		
1.25	FLM-1.25	FLQ-1.25	FNQ-R-1.25		
1.5	FLM-1.5	FLQ-1.5	FNQ-R-1.5		
2.0	FLM-2	FLQ-2	FNQ-R-2		
2.5	FLM-2.5	FLQ-2.5	FNQ-R-2.5		
3.0	FLM-3	FLQ-3	FNQ-R-3		
4.0	FLM-4	FLQ-4	FNQ-R-4		
5.0	FLM-5	FLQ-5	FNQ-R-5		
7.0	FLM-7	FLQ-7	FNQ-R-7		
10.0	FLM-10	FLQ-10	FNQ-R-10		
15.0	FLM-15 (125 VAC)	FLQ-15	FNQ-R-15		
20.0	FLM-20 (32 VAC)	FLQ-20	FNQ-R-20		
30.0	FLM-30 (32 VAC)	FLQ-30	FNQ-R-30		
AMP RATING	600V M	600V MODEL			
3.0A	KLK-	-3			






SP

APPLICATION

- FLM/FLQ/FNQ Series Inductive loads, power supplies, control transformers, control circuits with high inrush currents
- KLK-3 Watt meters, watt transducers, and control circuits without high inrush currents
- FLM/FLQ/KLK UL File E19180; FNQ UL File E4273



DESCRIPTION

GF and **K235** series glass fuses are available in slow-blow and fast-acting models.

FEATURES


- GF Series for use with M10/16SFL fuse holder, HKP-HH and HRK
- K235 Series for use with M4/8 and ZS4 Series Disconnect Switch and Fuse Holders
- GF & K235 UL File E19180; HKP-HH & HRK UL File E72169

SPECIFICATIONS / ORDERING INFORMATION (Order QTY 1 = standard package of 5) Ex. 5 GF-5 = 25 fuses

AMP RATING	VOLTAGE	FAST-ACTING FUSE	SLOW-BLOW FUSE	FAST-ACTING
0.5	250	GF-0.5	GF-0.5S	K235-0.5
1	250	GF-1	GF-1S	K235-1
1.5	250	GF-1.5	GF-1.5S	K235-1.5
2	250	GF-2	GF-2S	K235-2
2.5	250	GF-2.5	GF-2.5S	K235-2.5
3	250	GF-3	GF-3S	K235-3
5	250	GF-5	GF-5S	K235-5 (125V)
7	250	GF-7	GF-7S	K235-7 (125V)
10	250	GF-10	GF-10S*	K235-10 (125V)
15	250	GF-15*	GF-15S*	

HRK Inline fuseholder, 32V, 15A, for 1/4" fuses 7/8"-1-1/4" HKP-HH Panel mount fuseholder, 250V, 15A, for 1/4" x 1-1/4" fuses

GF, K235 Series HKP-HH CUL UR



DESCRIPTION

251 Series fast-acting circuit board type fuses are sold in packs of 5 and range from 0.125 A to 2.0 A ratings.

SPECIFICATIONS / ORDERING INFORMATION (Sold in packs of 5) (Order QTY 1 = PACKAGE of 5)				
AMP RATING	125V MODEL			
1/8	#251.125			
1/2	#251.500			
1	#251001			
2	#251002			



APPLICATION

WHEN YOU NEED IT RIGHT, RIGHT NOW, CALL KELE.

UL File E19180

DIMENSIO	DNS
in (cm)	0.28 1.47 (3.74) (0.70) (0.70) (0.238) dia

Ceramic tube fuse