RANGEABLE PRESSURE TRANSMITTER

GC51 SERIES

DESCRIPTION

The Ashcroft GC51 Rangeable Pressure Transmitter is a compact alternative to the conventional process transmitter available in compound and gauge ranges. The ranges span from Vacuum to 15 PSI, 30 PSI, or 50 PSI compound ranges and 0 to 7500 PSI ranges. The **GC51 Series** features a two wire 4-20mA output, backlit LCD display, stainless steel wetted parts, and NEMA 4X, IP65, robust aluminum housing. The range and output allows for rescaling and setting of user defined units.


FEATURES

- · NEMA 4X (IP65) aluminum die cast housing
- · Backlit LCD display
- · Min./Max. hold to capture pressure events
- · Rotatable display
- Adjustable pressure range and output
- 2 wire 4-20mA output
- · Standard 120ms response time
- · Internal push button keys with key lock feature
- · Optional NIST certification





CE



SPECIFICATIONS

Supply Voltage 12-32 VDC Signal Output 4-20 mA (2-wire) **Maximum Output** 545Ω @ 24 VDC Impedance mA

Adjustments Zero and Span Adjustable -10% to 110% FS

±0.25% Full Scale (includes linearity, **Accuracy** hysteresis, and repeatability) ±0.02% FS (URL)/°C from 23°C reference

Thermal Effect Overpressure (Proof) 1500 psi FS and below

200% FS value 3000, 5000 psi 150% FS value 120% FS value 7500 psi

Measurement Range Vac-15 psi (-101.6 Vac to 103.4 KPa) to Display

Type Accuracy Operating Temperature Wetted Parts **Storage Temperature**

Enclosure Rating Process Connection Wiring Terminations

Approvals Weight Warranty

0-7500 psi (0-51710.68 KPa)

4 digit, 10mm LCD with LED backlight ±0.25% FS (URL) + last digit -10° to 60°C (14° to 140°F) 316 Stainless Steel and 17-4PH SS -20° to 70°C (-4° to 158°F) Epoxy coated aluminum, NEMA 4X (IP65) 1/4 FNPT

Cable Gland (Cable Diameters 0.35" to 0.47")

ČE Approx. 1.0 lb (0.45 kg)

1 year

ORDERING INFORMATION

MODEL GC51-15V GC51-30V GC51-50V GC51-50 GC51-100 GC51-150	DESCRIPTION Pressure transmitter, Vac to 15 psi Pressure transmitter, Vac to 30 psi Pressure transmitter, Vac to 50 psi Pressure transmitter, 0-50 psi Pressure transmitter, 0-100 psi Pressure transmitter, 0-150 psi
GC51-300 GC51-500 GC51-1000	Pressure transmitter, 0-300 psi Pressure transmitter, 0-500 psi Pressure transmitter, 0-1000 psi
GC51-1500 GC51-3000 GC51-5000 GC51-7500	Pressure transmitter, 0-1500 psi Pressure transmitter, 0-3000 psi Pressure transmitter, 0-5000 psi Pressure transmitter, 0-7500 psi Pressure transmitter, 0-7500 psi

	RELATED PRODUCTS	PAGE
PT	1/4" pigtail syphon with fittings	1112
DCPA-1.2	Power supply, 120 VAC In to 24 VAC/24 VDC Out	994
DCP-1.5-W	Power supply, 24 VAC IN to 24 VDC OUT	995
47B-1	Brass piston style snubber	1112
47S-1	Stainless steel piston style snubber	1112

NEW!