

# ENCLOSURES

## SAGINAW NEMA 4 ENCLOSURES AND PANELS H-LP SERIES




5

ENCLOSURES

### DESCRIPTION


The Saginaw H-LP Series NEMA 4 enclosures are designed to house electrical and pneumatic controls, instruments, and components. These enclosures provide protection from windblown dust and rain, splashing water, and hose-directed water.



H-LP Series

### FEATURES

- Continuously welded or ground-smooth seam, no holes or knockouts
- Seamless, watertight foam gasket for tight seal
- Hasp and staple for padlocking
- Collar studs provided for mounting optional subpanels
- Steel subpanels available
- UL File #E69392
- CSA certified
- One-year warranty



### ORDERING INFORMATION

ENCLOSURE			SOLID STEEL PANEL		
MODEL	DIMENSIONS A x B x C in (cm)	WEIGHT lb (kg)	MODEL	DIMENSIONS A x B in (cm)	WEIGHT lb (kg)
SCE16H1206LP+	16 x 12 x 6 (40.7 x 30.5 x 15.2)	21 (9.5)	SCE16P12	13 x 9 (33 x 22.9)	4 (1.8)
SCE16H1208LP+	16 x 12 x 8 (40.7 x 30.5 x 20.3)	22 (10)	SCE16P12	13 x 9 (33 x 22.9)	4 (1.8)
SCE16H1606LP+	16 x 16 x 6 (40.6 x 40.6 x 15.2)	27 (12.3)	SCE16P16	13 x 13 (33 x 33)	6 (2.7)
SCE20H1606LP+	20 x 16 x 6 (50.8 x 40.6 x 15.2)	30 (13.6)	SCE20P16	17 x 13 (43.2 x 33)	8 (3.6)
SCE20H1608LP+	20 x 16 x 8 (50.8 x 40.6 x 20.3)	31 (14.1)	SCE20P16	17 x 13 (43.2 x 33)	8 (3.6)
SCE20H2006LP+	20 x 20 x 6 (50.8 x 50.8 x 15.2)	34 (15.5)	SCE20P20	17 x 17 (43.2 x 43.2)	10 (4.5)
SCE20H2008LP+	20 x 20 x 8 (50.8 x 50.8 x 20.3)	33 (15)	SCE20P20	17 x 17 (43.2 x 43.2)	10 (4.5)
SCE24H2006LP+	24 x 20 x 6 (61 x 50.8 x 15.2)	39 (17.7)	SCE24P20	21 x 17 (53.3 x 43.2)	14 (6.4)
SCE24H2008LP+	24 x 20 x 8 (61 x 50.8 x 20.3)	43 (19.5)	SCE24P20	21 x 17 (53.3 x 43.2)	14 (6.4)
SCE24H2406LP+	24 x 24 x 6 (61 x 61 x 15.2)	43 (19.5)	SCE24P24	21 x 21 (53.3 x 53.3)	17 (7.7)
SCE24H2408LP+	24 x 24 x 8 (61 x 61 x 20.3)	50 (22.7)	SCE24P24	21 x 21 (53.3 x 53.3)	17 (7.7)
SCE30H2406LP+	30 x 24 x 6 (76.2 x 61 x 15.2)	56 (25.5)	SCE30P24	27 x 21 (68.6 x 53.3)	22 (10)
SCE30H2408LP+	30 x 24 x 8 (76.2 x 61 x 20.3)	61 (27.7)	SCE30P24	27 x 21 (68.6 x 53.3)	22 (10)
SCE30H3008LP+	30 x 30 x 8 (76.2 x 76.2 x 20.3)	74 (33.6)	SCE30P30	27 x 27 (68.6 x 68.6)	28 (12.7)
SCE36H2406LP+	36 x 24 x 6 (91.4 x 61 x 15.2)	63 (28.6)	SCE36P24	33 x 21 (83.8 x 53.3)	27 (12.3)
SCE36H2408LP+	36 x 24 x 8 (91.4 x 61 x 20.3)	65 (29.5)	SCE36P24	33 x 21 (83.8 x 53.3)	27 (12.3)
SCE36H3008LP+	36 x 30 x 8 (91.4 x 76.2 x 20.3)	84 (38.2)	SCE36P30	33 x 27 (83.8 x 65.6)	34 (15.5)

+Add P to the end of the part number to order optional perf panel and order panel separately.