



PANEL FABRICATION

TOGGLE SWITCHES 23F, 21F, 41F SERIES

DESCRIPTION

23F, 21F, and 41F Series Toggle Switches are general-purpose toggle switches for pilot duty control of electric equipment such as fans, pumps, and compressors or control of electric control circuits.


FEATURES

- *Non-corrosive, phenolic, and metal housing*
- *Durable, slow make/slow break, contact mechanism*
- *Simple installation requires single hole*
- *Conveniently installed with one hexagon locknut and one knurled facenut (furnished)*
- *Compression spring provides positive contact pressure in closed position*

DIMENSIONS

in
(cm)

Mounting hole
0.5" (1.27) diameter



Typical Switch

SWITCH	A	B	H	W	D
Single Pole	0.687 (1.74)	0.465 (1.18)	0.67 (1.70)	1.134 (2.88)	0.634 (1.61)
Double Pole	0.687 (1.74)	0.465 (1.18)	0.778 (1.98)	1.308 (3.32)	0.75 (1.91)
Three Pole	0.687 (1.74)	0.465 (1.18)	0.803 (2.04)	1.308 (3.32)	1.088 (2.76)
Four Pole	0.687 (1.74)	0.465 (1.18)	1.218 (3.09)	1.44 (3.65)	1.34 (3.41)

SSG1-1/2

SYZE-074



SPECIFICATIONS

Contacts rated	10A @ 250 VAC 15A @ 125 VAC 3/4 hp, 120-240 VAC
Housing	Phenolic, metal
Metal parts	Bright nickel-plated brass
Mounting	Single hole type, 0.5" dia (1.27 cm)
Terminals	Screw
Agency approvals	UL-recognized component, File #E7560; CSA certified, File #LR9280
Warranty	1 year

ORDERING INFORMATION

MODEL	DESCRIPTION	MODEL	DESCRIPTION
23F341	Toggle switch SPST on-off	21F905	Toggle switch 3PST on-off
23F345	Toggle switch SPDT on-on	21F911	Toggle switch 3PDT on-on
23F343	Toggle switch SPDT on-off-on	21F908	Toggle switch 3PDT on-off-on
23F347	Toggle switch DPST on-off	41F562	Toggle switch 4PST on-off
23F357	Toggle switch DPDT on-on	41F564	Toggle switch 4PDT on-on
23F349	Toggle switch DPDT on-off-on	41F563	Toggle switch 4PDT on-off-on

LEGEND PLATES

MODEL	DESCRIPTION
SYZE-074	On/Off plate
SYZE-075	Summer/Winter plate
SYZE-212	On/Off/Auto plate
SYZE-255	Summer/Off/Winter plate

RELATED PRODUCTS

SSG1 - 1/2 Wall plate box mount 1/2" hole