



ENCLOSURES

KELE CONTROL COMPONENT MOUNTING PANEL PERF PANEL

DESCRIPTION

Kele Perf Panels easily mount control components in standard control enclosures and are a product normally stocked by Kele. **Perf Panels** are made from perforated 16-gauge steel and feature a gray powder-coated finish. Prepunched holes allow for mounting almost any device without drilling. Simply set the control components on the panel and attach with #7 or #8 self-tapping screws. RET Enclosures come standard with **Perf Panels**. Hoffman NEMA 1, 3R & 4 enclosures, H series, non-metal and C-SD Concept series enclosures featured in the Kele catalog can be ordered with a perforated panel. Custom sizes may also be ordered.



RP2620
with Perf Panel mounted

SIZE (SAMPLE)



Actual Size (sample)
16 ga steel, hole 1/8" staggered
All flanges are 1/2" depth

ORDERING STANDARD PERFORATED PANELS

Perf #*	Size (in) H x W	Flat/ Flanged	Perf #	Size (in) H x W	Flat/ Flanged	Perf #	Size (in) H x W	Flat/ Flanged
HP66	4.25" X 4.25"	Flat	RP2620	23.5" X 17.5"	Flanged	CSP2020	18.2" X 18.2"	Flanged
HP86	6.25" X 4.25"	Flat	RP3626	33.25" X 23.25"	Flanged	CSP2416	22.2" X 14.2"	Flanged
HP88	6.25" X 6.25"	Flat	RP3826	35.5" X 23.5"	Flanged	CSP2421	22.2" X 18.2"	Flanged
HP108	8.25" x 6.25"	Flat	RP4230	39.25" x 27.25"	Flanged	CSP2424	22.2" X 22.2"	Flanged
HP1010	8.25" x 8.25"	Flat	ST86	6.75" X 4.88"	Flat	CSP3024	28.2" X 22.2"	Flanged
HP128	10.25" x 6.25"	Flat	ST108	8.75" X 6.88"	Flat	CSP3624	34.2" X 22.2"	Flanged
HP1210	10.25" x 8.25"	Flat	ST1210	10.75" X 8.88"	Flat	CSP3630	34.2" X 28.2"	Flanged
HP1211	10.25" x 9.25"	Flat	ST1412	12.88" X 10.88"	Flat	CSP3636	34.2" X 34.2"	Flanged
HP1212	10.25" x 10.25"	Flat	ST1614	14.88" X 12.88"	Flat	CSP4236	40.2" X 34.2"	Flanged
HP1412	12.25" x 10.25"	Flat	ST1816	16.88" X 14.88"	Flanged	CSP4836	46.2" X 34.2"	Flanged
HP1612	14.25" x 10.625"	Flat	ST2016	17" X 13"	Flanged	CSP6036	58.2" X 34.2"	Flanged
HP1616	13" x 14.5"	Flanged	ST2412	21" X 9"	Flanged	HO1612	13" X 9"	Flat
HP1620	13" x 18.5"	Flanged	ST2424	21" X 21"	Flanged	HO1616	13" X 13"	Flat
HP1812	16.25" x 10.25"	Flanged	ST3020	27" X 17"	Flanged	HO2016	17" X 13"	Flanged
HP1818	16.25" X 16.25"	Flanged	ST3024	27" X 21"	Flanged	HO2020	17" X 17"	Flanged
HP2012	18.25" x 10.25"	Flanged	ST3630	33" X 27"	Flanged	HO2416	21" X 13"	Flanged
HP2016	17" x 14.5"	Flanged	IP66	4.88" X 4.88"	Flat	HO2420	21" X 17"	Flanged
HP2020	17" x 18.5"	Flanged	IP86	6.75" X 4.88"	Flat	HO2424	21" X 21"	Flanged
HP2416	21" x 14.5"	Flanged	IP88	6.75" X 6.75"	Flat	HO3024	27" X 21"	Flanged
HP2420	21" x 18.5"	Flanged	IP108	8.75" X 6.88"	Flat	HO3030	27" X 27"	Flanged
HP2424	21" x 22.5"	Flanged	IP1210	10.75" X 8.88"	Flat	HO3624	33" X 21"	Flanged
HP3024	26" x 22.5"	Flanged	IP1412	12.75" X 10.88"	Flat	HO3630	33" X 27"	Flanged
HP3030	26" x 28.5"	Flanged	IP1614	14.75" X 12.88"	Flat	HO4224	39" X 21"	Flanged
HP3624	32" x 22.5"	Flanged	IP1816	16.75" X 14.88"	Flanged	HO4230	39" X 27"	Flanged
HP3630	32" x 28.5"	Flanged	CSP1212	10.2" X 10.2"	Flat	HO4236	39" X 33"	Flanged
QP1812	17" X 11"	Flat	CSP1612	14.5" X 10.2"	Flat	HO4836	45" X 33"	Flanged
RP1812	15.5" x 9"	Flanged	CSP2016	18.2" X 14.5"	Flanged	HO6036	57" X 33"	Flanged
RP2018	17.5" x 15.5"	Flanged						

* Add "-HW" suffix to include Perf Panel mounting hardware

ORDERING CUSTOM SIZE PERFORATED PANELS

MODEL
FT-H x W (in)
FL-H x W (in)

DESCRIPTION

Flat perf panel for enclosure smaller than 16" x 12" (40.6 x 30.5 cm)
Flanged perf panel for enclosure 16" X 12" or larger (40.6 x 30.5 cm)

Maximum painted flat/flanged panel 34" H x 58" W (86 x 147 cm),
Maximum unpainted flanged panel 34" H x 78" W (86 x 198 cm)

NOTE: Order custom perforated panels by exact outer size

Example: FT-14.5 x 10.25 flat perf panel, 14.50" x 10.25"

All above Perf Panels needs model Perf Hardware or order above panel with "-HW" to have included.