

# ALARMS AND INDICATION

## PLATE-MOUNTED EMERGENCY OPERATOR STATIONS

**WPS SERIES**



### DESCRIPTION

The **WPS Series Plate-Mounted Emergency Operator Stations** allow the mounting of an alarm initiator on a single-gang wall box or standard handy box. These come with brushed stainless steel plates for flush mounting and are rated NEMA 1 indoor. Many options are available for the **WPS Series** in addition to models on our catalog page.

### FEATURES

- Mounted on brushed stainless steel wall plate
- Order contacts separately for wiring flexibility
- Special configurations are available
- Special labeling is available
- Single-gang wall or handy box mounting
- Contacts rated 600V at 10A AC and 2.5A DC
- One-year warranty



WPS-TW-ST



WPS-MP-PO



WPS-KR-SO



WPS-RP1-ST



3

ALARMS & INDICATION

### ORDERING INFORMATION

MODEL	DESCRIPTION
WPS	Wall plate, box mounted emergency operator station (order contacts separately)
<b>BUTTON STYLE</b>	
MO	Red <b>momentary</b> 40 mm mushroom
MP	Red <b>maintained</b> 40 mm mushroom (push-pull) labeled "Pull to Reset"
TW	Red <b>maintained</b> 40 mm mushroom (push-turn to reset) labeled "Turn to Reset"
KR	Red <b>maintained</b> key release 40 mm mushroom with two keys, key required to reset only
RP1	Red "Raise Lid - Push Button" padlockable <b>solid</b> lid over <b>momentary</b> flush round push button
RP2	Red "Raise Lid - Push Button" padlockable <b>solid</b> lid over <b>maintained</b> flush round push button
CP1	Red "Raise Lid - Push Button" padlockable <b>clear</b> lid over <b>momentary</b> flush round push button
CP2	Red "Raise Lid - Push Button" padlockable <b>clear</b> lid over <b>maintained</b> flush round push button
<b>LEGENDS</b>	
CS	EMERGENCY - CHILLER STOP
PO	EMERGENCY - POWER OFF
BS	EMERGENCY - BOILER SHUT-DOWN
HS	EMERGENCY - HVAC SHUT-DOWN
VS	EMERGENCY - VENTILATION STOP
ST	EMERGENCY - STOP
SD	EMERGENCY - SHUT-DOWN
VSTART	EMERGENCY - VENTILATION START
SO	EMERGENCY - SHUT-OFF

**Example:** WPS-MP-VSTART Wall plate emergency operator station, red maintained push-pull button labeled "Ventilation Start"

WPS - MP - VSTART

### RELATED PRODUCTS

MODEL	DESCRIPTION
PILNCCB	Normally closed stackable contact block
PILNOCB	Normally open stackable contact block
PILRPKEY	Replacement key (specify model and key number)

Note: Three contact blocks can be used for a depth of 1-5/8" (42 mm).

Three more can be added for a depth of 2-5/8" (67 mm).