



ALARMS & INDICATION

PLATE MOUNTED OPERATOR STATIONS WPS SERIES

Pilla Electrical Products, Inc.

DESCRIPTION

The Pilla Electrical Products WPS Series plate-mounted operator stations mount on a single-gang wall box or a standard handy box and come with brushed stainless steel plate. They are rated NEMA 1 for indoor applications. Many options are available for the WPS Series in addition to the models shown on our catalog page. (***) Contact blocks are not included and need to be ordered separately.)

FEATURES

- Order contacts separately for wiring flexibility
- Hinged lockout lids options
- Single-gang wall or handy box mounting

SPECIFICATIONS

Contact Rating	600 V at 10A AC 2.5A DC
Additional Specifications	Related Products Note: Three contact blocks can be used for a depth of 1-5/8" (42 mm). Three more can be added for a depth of 2-5/8" (67 mm).
Approvals	UL File E158147
Enclosure Rating	NEMA 1
Warranty	1 year



WPS-MP-BS-CLM



WPS-KR-VS



WPS-BR-PO



WPS-RP2-HS




WPS-MO-PO-DLM



ORDERING INFORMATION

MODEL	DESCRIPTION
WPS	Wall plate, box mounted emergency operator station (contacts not included)
BUTTON STYLE	
MO	Red momentary 40 mm mushroom
MP	Red maintained 40 mm mushroom (push-pull) labeled "Pull to Reset"
TW	Red maintained 40 mm mushroom (push-turn to reset) labeled "Turn to Reset"
KR	Red maintained key release 40 mm mushroom with two keys, key required to reset only
RP1	Red "Raise Lid - Push Button" padlockable solid lid over momentary flush round push button
RP2	Red "Raise Lid - Push Button" padlockable solid lid over maintained flush round push button
CP1	Red "Raise Lid - Push Button" padlockable clear lid over momentary flush round push button
CP2	Red "Raise Lid - Push Button" padlockable clear lid over maintained flush round push button
BR	Break Lens model with hammer
LEGENDS	
CS	EMERGENCY - CHILLER STOP
PO	EMERGENCY - POWER OFF
BS	EMERGENCY - BOILER SHUT-DOWN
HS	EMERGENCY - HVAC SHUT-DOWN
VS	EMERGENCY - VENTILATION STOP
ST	EMERGENCY - STOP
SD	EMERGENCY - SHUT-DOWN
VSTART	EMERGENCY - VENTILATION START
SO	EMERGENCY - SHUT-OFF
CLM	Clearhinged lockout lid for use with MO, MP, TW, KR 40mm mushroom button
DLM	Hinged lockout lid for use with MO 40mm mushroom button. Requires lid to be lifted in order to automatically release/extend mushroom device.

Example: WPS-MP-VSTART Wall plate operator station red maintained push-pull button labeled "Ventilation Start"



RELATED PRODUCTS

- PILKBR
- PILNCCB
- PILNOCB
- PILCLM
- PILRPKEY
- PILBRLNS

N.C. / N.O. contact block for the model "BR" break lens unit only.
 N.C. stackable contact block
 N.O. stackable contact block
 Clear cover for MO, MP, TW, KR stations
 Replacement key for WPS-KR series, specify model and key number when ordering
 Replacement lenses for WPSBR models only (3/pkg)

Note: Three contact blocks can be used for a depth of 1-5/8" (42 mm).
 Three more can be added for a depth of 2-5/8" (67 mm).