

VG210R 15-50BS



SPECIFICATIONS

Design	Two Way Plug Valve, Stem up closed.
Pressure Class	PN 16
Flow Characteristic	Equal percentage, modified (for finer opening control)
Stroke	11 mm
Rangeability	> 100:1
Leakage	<0.005% (to EN60534-4 Class IV-S1)
ΔP_m^a	600 kPa, water
Media Compatibility	Chilled or hot water, 60% glycol concentration, low pressure conditioned steam.
Media Temperature	-7° to +150° C
Maximum Steam Pressure	.241 kPa
Connection	Rp to ISO 7-1/BS21 Rg to ISO228-1

a. ΔP_m : Maximum allowable pressure drop across a fully open valve.

Suitable Actuator

Direct fit MG600C, MG600C SR
With AV-823 Long Stem adaptor . . . M400, M800,
M1500 and MG900 SR

Materials

Body . . Bronze; ASTM B584; CDA 83450 Oshalloy
Bonnet/Packing Cartridge. . . Brass; UNS C36000
and PTFE/EPDM chevrons
Stem AISI 316 SS
Plug AISI 316 SS
Seat Seal PTFE, DN 15-20, EPDM, DN 25-50
Slotted Stem Adapter RoHS compliant
Zinc-plated steel

The installer/product specifier must verify media compatibility of the valves construction materials with the water treatment/heat transfer solution supplier.

A strainer should be fitted upstream of the valve to increase valve reliability and protection of gland and seat seals.

Adherence to water treatment guidelines as detailed in VDI 2035 must be followed. Valves should be installed in the return pipe to reduce exposure to media temperature extremes.

Two Way High Performance Globe Valves, Bronze Body with Stainless Trim

The New Venta VG210R 15-50BS is a new range of precision bronze globe valves, suitable for a demanding fluid control applications with large differential pressure drops, including heating, cooling, air handling and domestic hot water systems. The VG210R 15-50BS series works reliably under a wide variety of conditions, including fluids with high glycol concentrations and very high temperature bands.

The valve utilises precision plugs for improved rangeability and fine fluid control on small opening degrees. Soft seating also ensures no seepage of precious energy when not required.

The VG210R 15-50BS range of valves is designed to be used in conjunction with the new short yoke Forta, providing one of the most compact plant room globe valves on the market. This enables the product to be fitted within conventional ceiling voids.

KEY FEATURES

- U-bolt bonnet and slotted stem adaptor provides quick and simple mounting with the short yoke Forta actuator
- RoHS compliant
- Stainless steel trim for wide media compatibility and large pressure drops
- High rangeability provides fine accurate fluid control for more efficient, responsive and comfortable regulation
- Tight sealing with zero energy leakage on shutoff for improved system efficiency
- Compact Space envelope

PRODUCT SELECTION / CLOSE-OFF PRESSURE RATINGS

ΔP_c Close-off performance with MG600C (-SR) Actuator

Size (DN)	Kvs	Connection	Part Number	Type Designation	Rangeability	ΔP_c Close Off (kPa) to Leakage Class	
						Class IV-S1 $\leq 0.005\%$	IV ¹ $\leq 0.01\%$
15	0.4	Rp 1/2	VG210R-15BS02	VG210R 15BS 0.4T SU00	100:1	1600	1600
15	0.63	Rp 1/2	VG210R-15BS03	VG210R 15BS 0.63T SU00			
15	1.0	Rp 1/2	VG210R-15BS04	VG210R 15BS 1T SU00			
15	1.6	Rp 1/2	VG210R-15BS05	VG210R 15BS 1.6T SU00			
15	2.5	Rp 1/2	VG210R-15BS07	VG210R 15BS 2.5T SU00			
15	4.0	Rp 1/2	VG210R-15BS08	VG210R 15BS 4T SU00			
20	6.3	Rp 3/4	VG210R-20BS	VG210R 20BS 6.3T SU00		1100	1200
25	10	Rp 1	VG210R-25BS	VG210R 25BS 10E SU00			
32	17	Rp 1-1/4	VG210R-32BS	VG210R 32BS 17E SU00			
40	24	Rp 1-1/2	VG210R-40BS	VG210R 40BS 24E SU00			
50	35	Rp 2	VG210R-50BS	VG210R 50BS 35E SU00		90	240

¹ Leakage class to as a percentage of a valves to Kvs, EN60534-4 with MG600C (-SR) actuator only

ΔP_c Close-off performance (kPa) with other Forta actuators (Long Stem adaptor required)

Actuator ² : Long stem adaptor: Leakage class ¹ :		M400		M800		M1500		MG900 SR	
		AV-823		AV-823		AV-823		AV-823	
		IV-S1	IV	IV-S1	IV	IV-S1	IV	IV-S1	IV
Part Number	DN	$\leq 0.005\%$	$\leq 0.01\%$	$\leq 0.005\%$	$\leq 0.01\%$	$\leq 0.005\%$	$\leq 0.01\%$	$\leq 0.005\%$	$\leq 0.01\%$
VG210R-15BS	15	1600	1600	1600	1600	1600	1600	1600	1600
VG210R-20BS	20								
VG210R-25BS	25	650	760	1550	1000	1170	1280	1000	1120
VG210R-32BS	32	350	440	950				640	750
VG210R-40BS	40	180	280	550	660	530	700	230	400
VG210R-50BS	50	30	140	230	350				

² MV15B, M700 and M3000 will not connect to the VG210R venta valve

¹ Leakage Class to EN60534-4 as a percentage of the valves Kvs

LEAKAGE NOTES:

The VG210R valves will provide tight shut from factory delivery, meeting EN60534-4 / VDI2173 to Class IV and Class IV-S1 depending on system pressure drops.

Application usage and system water quality can degrade O-ring performance against seat leakage over time.

RECOMMENDED ACTUATORS

This series of valves mounts directly on to the new short yoke Forta Actuators with U-Bolt Connection.




MG600C
Non Spring Return




MG600C SR
Spring Return

KEY FEATURES



#	Part	Description
1, 3	Plug and Seat Trim	AISI 316 stainless for cavitation resistance and long life
2	Internal Cavity	Carefully charted fluid dynamics to ensure low pressure drop and high flow capacity.
4	Packing	Triple-temp packing for use in cold water, hot water, and steam applications.
5	Body	Made from RoHS compliant materials.
6	Bonnet and Slotted Stem Adapter	Quick and simple mounting with the short yoke MG600C and MG600C-SR Actuators.


TYPE DESIGNATION



VALVE SIZING

Capacity Chart, Kvs

N.B. Capacity chart based on water with a Specific Gravity of 1.0



To size the ideal Kv, calculate pressure drops or refine selection sizing based on a glycol of density different to water, the following equations can be used.

For good fluid control and authority, the pressure drop through the valve should be as near as practicable equal to the pressure drop through the rest of the circuit which it controls.

$$Kv = Q \times \sqrt{\rho / \Delta P}$$

$$Q = Kv \times \sqrt{\Delta P / \rho}$$

$$\Delta P = \rho \times (Q / Kv)^2$$

Kv = Valve Capacity (m³/h)
Q = Volume flow (m³/h)
ΔP = Pressure drop across valve (bar)
ρ = Specific Gravity of fluid (kg/m³)

1 Bar = 100 kPa = 14.5 psi

1m³/h = 0.278 l/s = 0.167 l/min = 4.403 gpm (US)

DIMENSIONS mm

Size	L	H¹	H²
DN15	78	30	29
DN20	92		
DN25	118	44	30
DN32			37
DN40	137	46	40
DN50	156	57	57

Valve assembled onto MG600C actuator.

