

# TAMPER RESISTANT SUBSTATION



when **communication** is critical


## FEATURES

- Rugged Stainless Steel Faceplate
- No-Penetration Speaker Grill
- Microphone with a Preamplifier
- Nickel Plated Brass Call Buttons
- Epoxy Bonded Call-Connect LED
- Fits Standard 3-Gang Backbox
- Two Call Buttons
- Conformal Coated Board
- Transient Protection Built-In

## DESCRIPTION

The 6294-2 is a rugged tamper resistant substation with a unique design to protect the speaker, microphone, two call buttons, LED and internal electronics from external abuse. The station is ideal for jail cells, sally ports, external entryways and security intercom systems. The microphone, preamplifier, and speaker provide excellent sensitivity and voice quality. The 6294-2 provides clear, hands-free, two-way communication when called and will operate on all AlphaCom systems.

Note: Installer must drill weep holes in the bottom of backbox for outdoor installation.



## SPECIFICATIONS

FacePlate:	11 gauge, #304 stainless steel
Dimensions:	4 1/2" H x 6 1/4" W x 2 1/2" D
Speaker:	45 ohm, 2 3/4" oval, 1 watt
Push Button:	Two heavy duty stainless steel 5/8" inch buttons with machined stop
Preamplifier:	600 ohm output impedance, > 40 db s/n ratio
Connector: Screw Terminals	(4) 6" Pigtails
Cabling:	Requires (2) twisted pair #24 AWG to exchange
Mounting:	Standard (3) gang, deep, masonry box (by others) (Mounting screws not included)

www.stentofonusa.com

Zenitel USA  
6119 Connecticut Avenue  
Kansas City, MO 64120  
800/654-3140

ORDER NUMBER	DESCRIPTION	SHIP WEIGHT
100062942SMD	Tamper Resistant Substation	

TAMPER RESISTANT SUBSTATION

ORDER NUMBER

100062942SMD

sales@stentofonusa.com

STENTOFON products are developed and marketed by Zenitel USA. ZENITEL USA reserves the right to modify designs and alter specifications without prior notice, in pursuance of a policy of continuous improvement. © 2009 Zenitel USA.