

PANEL FABRICATION

WIRING AIDS AND DIN RAIL P, DN SERIES, DIN RAIL



DESCRIPTION

The **P Series Spiralite** is a universal spiral wrapping great for fast and economical grouping of wire bundles.

FEATURES

- **Polyethylene construction**
- **Flexible connection between panel and door**
- **Strong, yet simple to install and remove**

ORDERING INFORMATION

MODEL	FOR WIRE BUNDLES in (cm)	FT (m) (per carton*)
P2	1/4 to 1 (0.64 to 2.54)	80 (24)
P3	3/8 to 2 (0.95 to 5.08)	80 (24)
P4	1/2 to 3 (1.27 to 7.62)	65 (20)

* Available in carton quantities only – order quantity 1 = 1 carton



P Series

DESCRIPTION


DN Series Dinosaur Duct is flexible wiring duct for easy addition or removal of wiring.

FEATURES

- **Adhesive back for applications where mounting holes cannot be drilled**
- **Accommodates cables in restricted spaces**
- **Easily cut to desired length using scissors or knife**

ORDERING INFORMATION

MODEL	NOMINAL SIZE "H" x "W" (cm)	LENGTH in (cm)	PIECES (per carton)*
White			
DN10AW	1/2 x 1/2 (1.27 x 1.27)	19.5 (49.5)	42
DN20AW	3/4 x 3/4 (1.91 x 1.91)	19.5 (49.5)	64
DN30AW	1 x 1 (2.54 x 2.54)	19.5 (49.5)	36
DN40AW	1-1/2 x 1-1/2 (3.81 x 3.81)	19.5 (49.5)	20
Gray			
DN25AG	1 x 3/4 (2.54 x 1.91)	19.7 (49.5)	24
DN35AG	1-3/4 x 1-1/4 (4.45 x 3.18)	19.7 (49.5)	24
DN45AG	2-1/8 x 1-5/8 (5.4 x 2.64)	19.7 (49.5)	14



DN Series
* Ordered per piece


DESCRIPTION

DIN rail is the standard method for mounting relays and terminal blocks. Kele offers four models with different features.

FEATURES

- **One-meter length (39.4")**
- **Perforated**
- **Steel or aluminum**

DIMENSIONS




ORDERING INFORMATION

MODEL	DESCRIPTION	CARTON QTY*
DIN-3F	DIN rail, steel, RoHS compliant	40
DINRSTL	DIN rail, steel	100
BAM-1000	DIN rail, aluminum, extra depth	40
DINRALU	DIN rail, aluminum	100
DINCLIC-FM4	Mounting clips, 4 mm screw size	40

* Ordered per piece



BAM-1000
with DINCLIC-FM4
Mounting Clips



DIN-3F