

## Product data sheet

### Characteristics

## H222NRB

Safety switch, heavy duty, fusible, 60A, 2 poles, 15 hp, 240 VAC/250 VDC, NEMA 3R, bolt-on hub, neutral

Product availability : Stock - Normally stocked in distribution facility



Price\* : 842.00 USD



### Main

Product	Single Throw Safety Switch
Current Rating	60 A
Number of Poles	2
Voltage Rating	250 V DC 240 V AC
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	10 kA H or K 200 kA R, J or L
Mounting Type	Surface
Factory Installed Neutral	Neutral (factory installed)
Electrical Connection	Lugs
Duty Rating	Heavy duty
Certifications	UL listed file E2875
Enclosure Rating	NEMA 3R galvanized steel

### Complementary

Maximum Horse Power Rating	3 hp 240 V AC 50...60 Hz 1 phase NEC 240.6 7.5 hp 240 V AC 50...60 Hz 3 phase NEC 240.6 10 hp 240 V AC 50...60 Hz 1 phase NEC 430.52 15 hp 240 V AC 50...60 Hz 3 phase NEC 430.52 10 hp 250 V DC
Width	6.63 in (168.40 mm)
Height	14.88 in (377.95 mm)
Depth	4.88 in (123.95 mm)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 22, 2021

Tightening torque	50 lbf.in (5.65 N.m) AWG 3) 45 lbf.in (5.08 N.m) AWG 6...AWG 4) 40 lbf.in (4.52 N.m) 0.01 in <sup>2</sup> (8.367 mm <sup>2</sup> ) AWG 8) 50 lbf.in (5.65 N.m) 0.00...0.01 in <sup>2</sup> (2.06...5.261 mm <sup>2</sup> ) AWG 14...AWG 10)
-------------------	--

## Ordering and shipping details

Category	00009 - H&HU SW,2&3P,N3R,30-200A
Discount Schedule	DE1
GTIN	00785901478034
Nbr. of units in pkg.	1
Package weight(Lbs)	8.38 lb(US) (3.80 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.20 in (13.208 cm)
Package 1 width	7.70 in (19.558 cm)
Package 1 Length	16.20 in (41.148 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------