Catalog | March 2020



Harmony XB5R plastic and XB4R metal

Wireless and batteryless pushbuttons

www.schneider-electric.com

Life Is On





Quick access to product information

Get technical information about your product



Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:

- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Product image, Instruction sheet, User guide, Product certifications, End of life manual

Find your catalog



> With just 3 clicks, you can reach the Industrial Automation and Control catalogs, in both English and French

> Download Digi-Cat with this link

Select your training



Find the right <u>Training</u> for your needs on our Global website
 Locate the training center with the selector tool, using this <u>link</u>





- Updated quarterly
- Embeds product selectors and configurators,
- 360° images, training centersOptimized search by commercial reference







General contents

General presentation and selection guide	1
XB5R and XB4R wireless & batteryless pushbuttons	2
ZBRN1 and ZBRN2 Harmony hub	3
Product reference index	4

Contents

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Wireless and batteryless pushbuttons

Wireless and batteryless ecosystem devices

General presentation and selection guide

	Harmony XB4R and XB5R	
	Installation and maintenance	page 1/2
	Performance	page 1/3
	Range of products	page 1/3
	Harmony Hub ZBRN1 and ZBRN2	
	Installation and maintenance	page 1/4
	Performance and integration	page 1/4
	Architecture solutions	page 1/6
	Range of products	page 1/7
Se	election guide	page 1/8

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons

Installation made easy with Harmony[®] XB5R plastic and XB4R metal wireless and batteryless pushbuttons

The Harmony XB5R plastic and XB4R metal range of wireless and batteryless pushbuttons are used for various building utilities (automatic doors, lighting, etc.) and industrial applications (conveying systems, automotive, MMM, logistics, food and beverage). They are based on two types of device - transmitter and receiver - which communicate via 2.4 GHz radio transmission (free worldwide band).

Simplified installation

>

- Lower installation costs and time
 - No setup needed due to ready-to-use Plug-and-Play package
- > Freedom of mobility around the machine or process
- > Ideal solution when you need to add or move a control function



Enables end users to considerably reduce installation and maintenance costs

Easy maintenance

- > Requires no battery maintenance and helps to ensure permanent availability
- > Maximum availability of control functions
- > Eco-friendly Green technology
- > Minimizes post-installation maintenance

Product Selector

Web digital selector Click to open the selector

÷

1/2





Energy efficient due to non-current consuming transmitter

Robust performance

Designed for industrial environment with proven robustness

- > High resistance to contamination from dust (no cable entry)
- > No risk of cable damage or loose screws on the transmitter
- Ø 22 mm/0.866 in. operating head available in plastic (ZB5) and metal (ZB4) and Ø 40 mm/1.575 in. black spring return mushroom head allowing operation with gloves
- > For automatic doors, the rope pull switch command can be set anywhere
- Suitable for the most demanding environments, depending on the model, up to IP 66, for external use from -25 to 70 °C/-13 to 158 °F



Easy integration into automation products

1

General presentation (continued)

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons

Assured performance according to distance

- > 25 m/82 ft with the receiver installed in a metal electrical cabinet
- Boosted to more than 250 m/820 ft with the use of an external relay antenna with the receiver installed in a metal electrical cabinet



A worldwide range

>

> From individual products to ready-to-use packs



Wide range of XB5R/XB4R individual products

- > Designed to meet the requirements of the most common applications
- Simple to order with only one reference number
- Easy to install with factory pre-programmed transmitter and receiver



(1) Only one transmitter per receiver (2) Up to 32 transmitters per receiver



Simple to order with ready-to-use packs

Schneider Belectric

General presentation (continued)

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem devices Harmony Hub ZBRN1 and ZBRN2

1





 (1) Typical values, which can be affected by the application environment
 (2) Reduction in distance when the Harmony Hub is placed in a metal housing or in a closed metal enclosure

Easy installation

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem devices Harmony Hub ZBRN1 and ZBRN2

Smooth integration

Integration into an industrial PC (IT/OT box) via Ethernet link with 2 RJ45.



Magelis iPC and Edge Box runs Node-RED to wire devices on the Industrial Internet of Things. Node-RED is a simple, open source graphical programming tool for designing the communication data flow from OT to IT. To enable connectivity to the EcoStruxure platform, you need to have an industrial PC (IT/OT box) to push your collected physical signals and ensure immediate access to relevant data. This data-driven approach helps to improve a company's productivity and efficiency. Compatible Schneider Electric commercial references: HMIBMO* For more information, go to: <u>www.schneider-electric.com/hmi</u>



20% lower installation costs compared to a hard-wired solution

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem devices Harmony Hub ZBRN1 and ZBRN2

Architecture solutions

> Call to maintenance EcoStruxure architecture



With Harmony Hub ecosystem devices, there are multiple use cases:

- Pushbutton to call for maintenance, call for material, call for finished goods, and call for final products inspection
- Easily open internal automatic doors
- Identify which Emergency stop has been activated
- Help operators to react quickly in case of an anomaly
- Identify anomalies with the predefined threshold

1



Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem devices Harmony Hub ZBRN1 and ZBRN2



(1) Please refer to the reference tables on pages 3/3, 3/4, and 3/5.

Enhanced wireless ecosystem devices

1

Control and signaling units

Product

t type	Pilot lights	Pushbuttons, select	tor switches, and pilot ligh	nts	Biometric switches
			Th		
					0

protection IEC 60529 IP65 with seal Conforming to UL 508 and – Enclosure type 4, 4X, and 13	Description of r	ange	LED pilot lights	 Emergency Stop pu Selector switches a Illuminated pushbu Pilot lights 	 Multiple-headed pushbuttons Emergency Stop pushbuttons Selector switches and key switches Illuminated pushbuttons Pilot lights Flush mounted pushbuttons, selector switches, and pilot lights (1) 		
Shape of head Circular Circular, square, or rectangular Circular Circular	Features	Products		Complete units or sub-	· · · · · · ·		
Drilling or cut-out for fixing Ø 8 mm and Ø 12 mm/0.315 in. and 0.472 in. Ø 16 mm/0.630 in. Ø 22 mm/0.866 in. Ø 22 mm/0.866 in. Degree of protection Conforming to UL 508 and IP40 IP65 with seal IP65 IP66, IP67, IP69, and IP69K IP65 (control button) Enclosure type 4, 4X, and 13 Enclosure type 12		Bezel	Double insulated	Double insulated (4)			,
mm/0.315 in. and 0.472 in. Ø 30 mm/1.181 in. (for flush mounted control and signaling units) Degree of protection Conforming to IEC 60529 IP40 IP65 with seal IP65 IP66, IP67, IP69, and IP69K IP65 (control button) Conforming to UL 508 and - Enclosure type 4, 4X, and 13 Enclosure type 12			Circular or square	-			
protection IEC 60529 IP65 with seal Conforming to UL 508 and - Enclosure type 4, 4X, and 13	Drilling or cut-out for fixing		mm/0.315 in. and	Ø 16 mm/0. <i>630 in.</i>	Ø 30 mm/1.181 in.		Ø 22 mm/0.866 in.
UL 508 and				IP65	IP66, IP67, IP69, and IP69K		IP65 (control button)
USA UZZ-Z INU. 14			-	Enclosure type 4, 4X, a	losure type 4, 4X, and 13		Enclosure type 12
CablingTags for 2.8 x 0.5 mm/0.110 x 0.020 in. connectors or threaded connectorFaston connectors Solder pins for printed circuit boards (4) Fast connector socket (5)Spring clamp terminal connections Screw clamp terminal connections Faston connectors Connector with adapter for printed circuit board connector with adapter for printed circuit boardCable or connectors Connectors	Cabling		2.8 x 0.5 mm/0.110 x 0.020 in. connectors or threaded	Ox Solder pins for printed Screw clamp terminal connections rs circuit boards (4) Faston connectors Fast connector Connector with adapter for printed circuit board		Cable or connectors	
Mounting Panel thickness 18 mm/ 16 mm/0.0390.236 in.	Mounting	Panel thickness		16 mm/0.0390.23	86 in.		
Type references XVLA XB6, XB6E XB4 XB5 XB5S	Type references	5	XVLA	XB6, XB6E	XB4	XB5	XB5S

(1) Flush mounted control and signaling units are available for Harmony XB4 and XB5 ranges only.
 (2) Compatible with Magelis iPC, STU, OT, GXO, GT (except GT1000 series), GK, GH, and GTO models.
 (3) Wireless and batteryless pushbutton and receiver ready-paired at the factory.

Wireless and batteryless pushbuttons	Pushbuttons, selector switches, and pilot lights	Joystick co	ontrollers		Pushbuttons, selector switches, and pilot lights	Cam switches
				1		
		F				
 Wireless and batteryless pushbuttons and rope pull switch Wireless receivers Harmony Hub 	 Pushbuttons Emergency Stop and Emergency switching off pushbuttons Selector switches and key switches Illuminated pushbuttons Pilot lights 		rection or spring retur	n	 Pushbuttons Emergency Stop pushbuttons Selector switches and key switches Illuminated pushbuttons Pilot lights 	 Switches Stepping switches Reversing and changeover switches Ammeter switches Voltmeter switches Reversing switches Star-delta and reversing star-delta switches Pole change switches
Ready-to-use packs (3) and "components" range	Monolithic		nits or sub-ass d with lever)	semblies	Complete units or sub-assemblies (body + head)	Complete units or sub-assemblies (body + front panel+ head)
Metal, chromium plated, or double insulated, black	Double insulated, dark gray (or white for pilot lights)	Metal, chror	nium plated	Double insulated, black	Metal, chromium plated, or do	uble insulated, black
ransmitter with circular nead	Circular	Circular			Hexagonal	Square
ð 22 mm/0.866 in.					Ø 30 mm/ <i>1.181 in</i> .	Ø 16 or Ø 22 mm/0.630 or 0.866 in.: series K10 Ø 22 mm/0.866 in. and multifixing: series K1/K2 4 holes, 48 or 68 centers: series K30K150
P65	IP65 (control buttons and pilot lights) IP54 (Emergency switching off pushbuttons)	IP65	IP66	IP65	IP66	IP65: series K10 IP40, IP65 with seal: series K1/K2 IP40: series K30…K150
Enclosure type 12	Enclosure type 3 (pushbuttons and Emergency stop) and 4 (pilot lights)	Enclosure ty	rpe 4, 4X and 7	13	Enclosure type 4 and 13 (9001K) Enclosure type 4, 4X, 13 (9001SK)	-
Vireless (transmitter) Through cable (receiver)	Screw and captive clamp terminal connections Faston clip connections (pilot lights)		aptive clamp	terminal cor	nections	
16 mm/0.0390.236 in.						0.56 mm/ <i>0.0200.236 in.</i> (depending on model)
XB5R, XB4R	XB7	XD4PA	XD2GA	XD5PA	9001K, 9001SK	K10, K1, K2, K30, K50, K63, K115, K150

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Wireless and batteryless pushbuttons

Harmony XB5R and XB4R wireless and batteryless pushbuttons

-	
	Presentationpage 2/2
	Description
	"Ready-to-use packs" ranges page 2/3
	"Components" range page 2/4
	References
	Ready-to-use packs page 2/5
	Transmitter components for wireless and batteryless pushbuttons
	Transmitter components for wireless and batteryless rope pull switch
	Configurable receivers page 2/7
	Accessories page 2/8

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons



2

Figure A: Radio transmission between 1 transmitter and 3 receivers



Figure B: Radio transmission between 3 transmitters and 1 receiver



Figure C: Rope pull switch for automatic doors

Presentation

The Harmony wireless and batteryless pushbuttons range enables remote control of a relay (receiver) by means of a pushbutton (transmitter). The control is by radio transmission where the transmitter is equipped with an electric generator that converts mechanical energy, produced when the pushbutton is pressed, to electrical energy. A radio-encoded message with a unique ID code is sent as a single pulse to one or more receivers located several dozen feet away (see Figure A). A single receiver can also be actuated by up to 32 different transmitters (see Figure B).

In order to avoid any conflict of multiple transmission from different transmitters, a minimum time frame of 10 ms is required between each radio transmission. Depending on the application, a relay-antenna can be used to get round an obstacle that impedes transmission or to increase the range (see Figure A and Figure B).

The possible distance (1) between a transmitter and a receiver is approximately: - 100 m/328 *ft* where there are no obstacles

- 25 m/82 ft if the receiver is installed in a metal housing or in a closed metal enclosure

- 300 m/984 ft if a relay-antenna is located between the transmitter and the receiver (receiver installed in a metal housing or in a closed metal enclosure)

These distances could be drastically reduced in industrial environments where factors such as radio interference, obstacles, or electromagnetic interference may impede the signal. As a consequence, some radio frames may not be received by the receiver.

The wireless and batteryless pushbutton reduces installation time and cost since no wiring and associated equipment is required between the transmitters and the control panel.

This technology also allows an operator to be mobile or to have a control mounted on board a vehicle (trolley, truck, etc.). The pushbutton is always available and requires no maintenance (no battery needed).

The mobile box **ZBRM21** or **ZBRM22** associated with its support function is adapted for static and mobile applications mounted on vehicles.

The range also includes a new wireless and batteryless rope pull switch designed for easy operation of automatic doors. This switch can be either mounted directly on the panel or between two ropes close to the automatic door. This enables the forklift driver or pedestrian to open or close the door by pulling the rope, where the mechanical energy produced is transmitted as a radio message to the receiver in the control panel (see Figure C).

This technology (radio-encoded message sent as a single pulse) cannot be used for hoisting applications ("up/down", "right-left" movements, etc.) or safety applications (Emergency Stop pushbuttons, etc.). For these applications, it is recommended that Harmony XB4 and XB5 wired pushbuttons or the XAC range of pendant control stations be used.

Environment

The performance features of the XB5R range conform to the following specifications:

- International standards and approvals:
- □ Wireless and batteryless pushbuttons: EN/IEC 60947-1, EN/IEC 60947-5-1, and
- UL 508, and CSA C22-2 No. 14

□ Transmitter/Receiver system: BT 2006/95/EC, CE: R&TTE 1999/5/EC, and EMC 2004/108/EC

- International certifications: UL, CSA, C-Tick, GOST, and CCC
- Radio agreements: ANATEL (Brazil), SRRC (China), FCC (USA), RSS (Canada), ICASA (South Africa), and ARIB T66 (Japan)

For more technical information, please refer to our website www.schneider-electric.com.

(1) Typical values, which can be affected by the application environment.

References: page 2/5

Description

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons



Description of the "Ready-to-use pack" ranges (1) Pack with configurable receiver (see Figure D)

This pack comprises:

- 1 A transmitter with a fixing collar for assembly with a pushbutton head and mounting in a Ø 22 mm/0.87 in. hole
- 2 A flush, spring return, plastic or metal pushbutton head
- 3 A set of 10 different colored caps that can be clipped onto the pushbutton head
- 4 A 24...240 V \sim configurable receiver, 2 relay outputs, with 2 buttons (teach and parameter setting) 5 and 6 indicating LEDs 6

Figure D: Pack with transmitter and configurable receiver



Figure E: Pack with transmitter and non-configurable receiver

Pack with non-configurable receiver (see Figure E) (1)

This pack comprises:

- 1 A transmitter with a fixing collar for assembly with a pushbutton head and mounting in a \emptyset 22 mm/0.87 *in*. hole
- 2 A flush, spring return, plastic or metal pushbutton head
- 3 A black cap that can be clipped onto the pushbutton head
- 4 A 24 V ---- non-configurable receiver, 1 relay output, without indicating LED or button



Figure F: Pack with transmitter in handy box and configurable receiver

Pack with handy box and configurable receiver (see Figure F)

This pack comprises:

- 1 A handy box containing a wireless and batteryless pushbutton with plastic head
- 2 A set of 10 different colored caps that can be clipped onto the pushbutton head
- 3 A 24...240 V \eqsim configurable receiver, 2 relay outputs, with 2 buttons (teach and parameter setting) 4 and 6 indicating LEDs 5

(1) The wireless and batteryless pushbutton and the receiver are factory-paired.

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons



Figure G: Pack with transmitter in handy box and non-configurable receiver

Description of the "Ready-to-use pack" ranges (1) (continued) Pack with handy box and non-configurable receiver (see Figure G)

This pack comprises:

- 1 A handy box containing a wireless and batteryless pushbutton with plastic head
- 2 A black cap that can be clipped onto the pushbutton head
- 3 A 24 V ---- non-configurable receiver, 1 relay output, without indicating LED or button

Description of the "Components" range

Components are sold separately to allow completion of existing applications or creation of specific applications:

- 1 A transmitter for assembly with pushbutton head and mounting in a Ø 22 mm/ 0.87 in. hole
- 2 A flush, spring return, plastic or metal pushbutton head
- 3 A plastic mushroom head
- 4 A plastic or metal fixing collar
- 5 An empty handy box
- 6 A set of 10 different colored caps or a set of 10 same color caps that can be clipped onto the pushbutton head
- 7 Empty plastic boxes (1 or 2 cut-outs) for wall mounting or on-board applications
- 8 A 24...240 V \eqsim configurable receiver, 2 relay outputs, with 2 buttons (teach and parameter setting) and 6 indicating LEDs
- 9 A 24 V --- configurable receiver, 4 PNP outputs, with 2 buttons (teach and parameter setting) and 6 indicating LEDs
- 10 A relay-antenna
- 11 A rope pull switch
- 12 ZBRM21 mobile box for 1 pushbutton
- 13 ZBRM22 mobile box for 2 pushbuttons
- 14 ZBRACS support for mobile box

(1) The wireless and batteryless pushbutton and the receiver are factory-paired.

References

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons

	Description	Transmitter type	Voltage	Receiver type	Reference	Weight
			receiver V			kg/lb
A 195 1- N Start C Start C	Packs comprising: - 1 wireless and batteryless pushbutton assembled on fixing collar - 1 receiver Pushbutton and receiver are factory-paired.	Wireless and batteryless pushbutton +Ø 22 mm/0.87 in. plastic head + 1 set of 10 different colored caps (1 cap to be selected and attached)	24240 ≂	Configurable receiver ZBRRA equipped with: - choice of 3 output functions (monostable, bistable, stop/start) - 2 relay outputs		0.230/0.507
		Wireless and batteryless pushbutton + Ø 22 mm/0.87 in. metal head + 1 set of 10 different colored caps (1 cap to be selected and attached)	_	type RT 3A (2) - 2 buttons (teach, parameter setting) - 6 indicating LEDs (power ON, function modes, output status, signal strength)	XB4RFA02	0.245/0.540
		Wireless and batteryless pushbutton + Ø 22 mm/0.87 in. plastic head + 1 black cap not attached	24	Non-configurable receiver equipped with monostable output function: - 1 relay output type RT 3A - without button - without button	XB5RFB01	0.230/0.507
		Wireless and batteryless pushbutton + Ø 22 mm/0.87 in. metal head + 1 black cap not attached	_	LED	XB4RFB01	0.245/0.540
	Packs comprising: - 1 wireless and batteryless pushbutton assembled on fixing collar, in handy box (3) - 1 receiver Pushbutton and receiver are factory-paired.	Wireless and batteryless pushbutton + Ø 22 mm/0.87 in. plastic head mounted in a handy box + 1 set of 10 different colored caps (1 cap to be selected and attached)	24240 ~~	Configurable receiver ZBRRA equipped with: - choice of 3 output functions (monostable, bistable, stop/start) - 2 relay outputs type RT 3A (2) - 2 buttons (teach, parameter setting) - 6 indicating LEDs (power ON, function modes, output status, signal strength)	XB5RMA04	0.250/0.551
		Wireless and batteryless pushbutton +Ø22 mm/0.87 in. plastic head mounted in a handy box + 1 black cap not attached	24	Non-configurable receiver equipped with monostable output function: - with 1 relay output type RT 3A - without button - without indicating LED	XB5RMB03	0.250/0.551

(1) Wireless and batteryless pushbutton and the receiver are factory-paired.

(2) Receivers are supplied set to monostable output function. The user can configure it to bistable and stop/start functions.

(3) Supplied with a magnet to be stuck on by the customer.

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Reference

ZBRT1

ZBRT2 (5)

ZB5RZA0

ZB4RZA0

ZB5RZC2

ZB5RTC2

ZB5RTA1

ZB5RTA2

ZB5RTA3

ZB5RTA331

ZB5RTA4

ZB5RTA432

ZB5RTA5

ZB5RTA6

ZB4RTA1

ZB4RTA2

ZB4RTA3

ZB4RTA331

ZB4RTA4

ZB4RTA432

ZB4RTA5

ZB4RTA6

Weight kg/lb

0.025/0.055

0.025/0.055

0.015/0.033

0.030/0.066

0.025/0.055

0.055/0.121

0.045/0.099

0.045/0.099

0.045/0.099

0.045/0.099

0.045/0.099

0.045/0.099

0.045/0.099

0.045/0.099

0.085/0.187

0.085/0.187

0.085/0.187

0.085/0.187

0.085/0.187

0.085/0.187

0.085/0.187

0.085/0.187

Wireless and batteryless pushbuttons

Transmitter components for wireless and batteryless pushbuttons

	Description	Type of push	Color
bF100704	Transmitter for wireless and batteryless pushbutton (1) (2)	1 radio frame sent when buttor is pushed	ı —
		1 radio frame sent when buttor	I –
		is pushed 1 radio frame sent when buttor	1
ZBRT1 ZBRT2		is released	
	Spring return pushbutton	Flush (plastic)	Without cap (3)
	heads for transmitter ZBRT1	N 7	1.1.7
2 3	ZBRI1	Flush (metal)	Without cap (3)
PF-100728			
	Spring return mushroom head for transmitter ZBRT1	Mushroom 40 mm/ <i>1.58 in.</i> (plastic)	Black
			Dii-
ZB5RZA0	Wireless and batteryless pushbutton including:	Mushroom 40 mm/ <i>1.58 in.</i> (plastic)	Black
	- a transmitter equipped with fixing collar		
PF 100710	- a spring return mushroom		
Har and the second s	head		
and the	Wireless and batteryless	Flush (plastic)	White
ZB4RZA0	pushbuttons including:		
	- a transmitter equipped with fixing collar		Black
PF100748	- a spring return pushbutton head with cap attached (4)		Green
	nead with cap attached (4)		Green
			White I on green background
			Red
			Neu
ZB5RTA4			White O on red background
			Yellow
100756A			Blue
bF1		Flush (metal)	White
			Black
ZB5RZC2			Green
			-
			White I on green background
PE-100757A			Red
He here here here here here here here he			
			White O on red background
			Yellow
Harmony Page 1			
			Blue
ZB5RTC2			
	(1) Fixing collar ZB5AZ009 (plasti		
	(2) Only heads ZB4RZA0 and ZB (3) Cap to be ordered separately.		
	(4) This cap is factory-assembled		
	(5) This transmitter is only compating $ZBRNe$ version > 1.2		

version \geq 2.0, and access point ZBRN• version > 1.2.











Schneider Belectric

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons



ZBRP1

XB5RP1US2



ZBRRA

Transmitter components for wireless and batteryless rope pull switch							
Description	Application	Reference	Weight kg/ <i>lb</i>				
Rope pull switch with wireless and batteryless transmitter	For automatic doors: The rope pull switch sends a radio message to the receiver in the control panel to open and close the door.	ZBRP1	0.150/0.331				
Rope pull switch with wireless and batteryless transmitter, and a universal support accessory ZBRAUS2	For automatic doors: The rope pull switch sends a radio message to the receiver in the control panel to open and close the door.	XB5RP1US2	0.259/0.571				

Configurable receivers								
Description	Output function	Output type	Receiver voltage V	Reference	Weight kg/ <i>lb</i>			
Configurable receivers (6) equipped with: - 2 buttons (teach and parameter setting) - 6 indicating LEDs (power ON, function modes, output status, signal strength)	Monostable	4 PNP outputs, 200 mA/24 V	24	ZBRRC	0.130/0.287			
	Monostable, bistable	2 relay outputs type RT 3A <i>(7)</i>	24240 ≂	ZBRRD	0.130/0.287			
	Monostable, bistable, stop/start	2 relay outputs type RT 3A (7)	24240 $\overline{\sim}$	ZBRRA	0.130/0.287			

(1) Fixing collar ZB5AZ009 (plastic) or ZB4BZ009 (metal) to be ordered separately.

(2) Only heads ZB4RZA0 and ZB5RZA0 are mechanically compatible.

(3) Cap to be ordered separately. Refer to the "Accessories" table on page 2/8.

(4) This cap is factory-assembled and cannot be removed (risk of damage).

(5) This transmitter is only compatible with receiver ZBRR• version \geq 2.0, relay antenna ZBRA1 version \geq 2.0, and access point ZBRN• version > 1.2.

(6) Each receiver can be actuated by up to 32 transmitters.

(7) Receivers are supplied set to monostable output function. The user can configure it to bistable and stop/start functions.

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons

)	E ZBA7235
	ZBA7331





Caps for Harmony pushbutte	on heads ZB5RZA0 and ZB	4RZA0			
Description	Background color	Marking	Sold in lots of	Unit reference	Weigh kg//
Sets of 10 different colored caps with identical marking	White	Without	10	ZBA71	0.010/0.02
(1)		"l" (black)	10	ZBA7131	0.010/0.02
		" † " (black)	10	ZBA7134	0.010/0.02
		"+" (black)	10	ZBA7138	0.010/0.02
	Black	Without	10	ZBA72	0.010/0.02
		"O" (white)	10	ZBA7232	0.010/0.02
		"+" (white)	10	ZBA7233	0.010/0.02
		" \$" (white)	10	ZBA7235	0.010/0.02
		"I" (white)	10	ZBA7237	0.010/0.02
	Green	Without	10	ZBA73	0.010/0.02
		"I" (white)	10	ZBA7331	0.010/0.02
		"+" (white)	10	ZBA7333	0.010/0.02
		"飰" white	10	ZBA7335	0.010/0.02
		"II" (white)	10	ZBA7336	0.010/0.02
	Red	Without	10	ZBA74	0.010/0.02
		"O" (white)	10	ZBA7432	0.010/0.02
	Yellow	Without	10	ZBA75	0.010/0.02
	Blue	Without	10	ZBA76	0.010/0.02
Set of 10 different colored caps with different markings (1)	White, black, green, red, ye white "I" on green backgrou background, white "O" on r white "O" on black backgro	und, black "l" on white ed background,	1	ZBA79	0.010/0.02
Set of 6 different colored cap	s White, black, green, red, ye	ellow, blue	1	ZBA80	0.010/0.02

(1) Cap can be clipped on at 90° steps, through 360°.

References (continued)

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless pushbuttons

		Accessories (continue	ed)				
2101A		Boxes for wireless and batter					
Let 132		Product	Application	Description	Sold in lots of	Unit reference	Weight kg/lb
Care and Car		Plastic empty mobile box (1) (4)	For mobile and static applications with wireless and batteryless	1 cut-out	1	ZBRM21	0.109/0.240
			pushbuttons	2 cut-outs	1	ZBRM22	0.110/0.243
	Plastic mobile box equipped with button(s) and transmitter(s), 1 set of caps	For mobile and static applications with wireless and batteryles pushbuttons	1 button with ZBRT1 transmitter	1	ZBRM21A0	0.150/0.331	
	E	transmitter(s), i set of caps	pushbuttons	1 button with ZBRT2 transmitter	1	ZBRM21B0	0.151/0.333
ZBRM22	ZBRACS			2 buttons with ZBRT1 transmitters	1	ZBRM22A0	0.194/0.428
F 132104A				2 buttons with ZBRT2 transmitters	1	ZBRM22B0	0.195/0.430
Standiar Deterte				1 button with ZBRT1 and 1 button with ZBRT2	1	ZBRM22AB0	0.195/0.430
0				1 button with ZBRT2 and 1 button with ZBRT1	1	ZBRM22BA0	0.195/0.430
			Special support for tube or wall specific for ZBRM21 and ZBRM22	-	1	ZBRACS	0.064/0.141
ZBRM22A0		Empty plastic boxes for wireless and batteryless	For static or on-board wireless and batteryless pushbuttons	1 cut-out	1	XALD01	0.136/0.300
101374		pushbuttons (2)		2 cut-outs	1	XALD02	0.193/0.426
	Other accessories						
	Relay-antenna (3)	Between transmitter and receiver Used to increase the range and/or get round obstacles	24240 V ≂ □ 5 m/16.4 ft cable □ 1 power-ON LED □ 2 LEDs reception/transmission	1	ZBRA1	0.200/0.441	
XALD02		Passive antenna	Passive antenna to pass through a wall, must be close to a relay antenna or a receiver	□ 2 antennas □ 0.9 m/2.95 ft cable □ 2 RF connectors	1	ZBRA3	0.010/0.328
PF100707		Vertical or horizontal support	Universal support for rope pull switch	A carabiner and a support to attach horizontally or vertically	1	ZBRAUS2	0.109/0.240
		Fixing collar	-	Plastic	10	ZB5AZ009	0.038/0.084
ZBRA1				Metal	10	ZB4BZ009	0.038/0.084
		Legend plate, 27 x 8 mm/ 1.06 x 0.32 in., for engraving	For sticking onto handy box ZBRM01, ZBRM21, and ZBRM22	Self-adhesive, blank, black background	10	ZBY0101T	0.005/0.011
ZBRA3		 (1) Cannot be used for wired condition (2) Box equipped with cable gland (3) Not wired to the receiver. (4) Compatible with ZBRT1 and 	nd outlets, compatible with Harmony	/ ZB5 pushbutton heads	S.		
ZBRAUS2							

Contents

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Wireless and batteryless ecosystem devices

Harmony Hub ZBRN1 and ZBRN2

Presentation	page	3/2
Description	page	3/2
References		
Configurable Harmony Hub	page	3/3
Communication module	page	3/3
Accessories	page	3/3
Compatibility		
Harmony Hub ecosystem devices	page	3/4

Presentation, description

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2



OEE monitoring production equipment

3



ZBRN1 front view



ZBRN1 underside view

Presentation

Harmony Hub provides network connectivity openness by operating as an intermediate device between the wireless devices and PLCs (programmable logic controllers) or industrial PCs (IT/OT box) that support the Modbus/TCP protocol. Harmony Hub can be used with transmitters such as XB4R and XB5R wireless and batteryless pushbuttons, rope pull switches, mushroom head pushbuttons, Emergency stop monitoring, wireless and batteryless limit switches, and temperature and energy sensors.

Harmony Hub provides an easy way to digitize your production line to improve overall equipment efficiency (OEE) by using a non-intrusive wireless system that is easy to connect to the IT system.

It collects physical signals from an operator interface or secondary sensing device to generate computed data information for CMMS tools and operation management tools.

Data can be analyzed through our dedicated EcoStruxure platform using "AVEVA Insight" software, "Maintenance Advisor" software, or our "Augmented Operator Advisor" on-premise application.

Depending on the application, an external or relay antenna can be used to improve signal reception. Harmony Hub can support up to 60 radio transmitters.

It can be configured using the jog dial and 7-segment display (configuration and diagnostic modes), SoMachine, Unity Pro software, a third-party FDT container using DTM (Device Type Manager) files (1)(2), or an SD card.





Description

Standard Harmony Hub with communication module (see figure A)

Harmony Hub ZBRN1 has an empty slot for the ZBRCETH communication module to support the Modbus/TCP protocol. This communication module has 2 standard Ethernet RJ45 connectors that provide connectivity for daisy chain operation and daisy chain loop operation (when used with Schneider Electric ConneXium Ethernet switches) and thus avoids the use of an external switch or hub.

- 1 ZBRN1 standard Harmony Hub (3)
- 2 ZBRN1 instruction sheet
- 3 ZBRCETH Modbus/TCP network communication module
- 4 ZBRCETH instruction sheet

Standard Harmony Hub (see figure B)

Harmony Hub ZBRN2 has 2 embedded RS485 connectors, which avoids the use of an external hub for RS485 serial line connection. The supported data rates are 1,200 bps, 2,400 bps, 4,800 bps, 9,200 bps, 9,600 bps, 38,400 bps, and

- 115,200 bps.
- 1 ZBRN2 Harmony Hub
- 2 ZBRN2 instruction sheet
- (1) For more information on SoMachine and Unity Pro software, please visit our website www.schneider-electric.com.
- (2) DTM is a software component file that enables the SoMachine or Unity Pro software to communicate with the connected system.
- (3) ZBRN1 must be plugged with a communication module, reference ZBRCETH for Modbus/ TCP protocol.

Figure B: ZBRN2: Harmony Hub for Modbus Serial Line communication

3/2

References

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2





ZBRN2



ZBRCETH



Configurable Harmony Hub Description Data Output type Receiver Reference Weight voltage V function kg/lb Monostable (adjustable 1 slot for ZBRCETH 24...240 \eqsim Configurable ZBRN1 0.270/0.595 Harmony Hub equipped with: - 7-segment display from 100 ms to communication module (to be 1s) - jog dial ordered - 8 LED indicators separately) (Power On, functions mode, communication status, signal strength) - external antenna Monostable 2 RS485 24...240 ≂ ZBRN2 0.263/0.580 connector and (adjustable connectors protective plug from 100 ms to providing connectivity for 1 s) Modbus RS485 Serial Line

Communication module					
Description	Characteristics	Communication port	Reference	Weight kg/lb	
Modbus/TCP network communication module	Modbus/TCP protocol with embedded Web pages in 5 languages for configuration, monitoring, and diagnostics	2 RJ45 connectors providing connectivity for daisy chain and daisy chain loop operation	ZBRCETH	0.044/0.097	

Accessories				
Product	Application	Description	Reference	Weight kg/ <i>lb</i>
External antenna	Connected to the Harmony Hub (ZBRN1 or ZBRN2) Used to increase the distance of transmission	2 m/6.56 ft cable 1 RF connector	ZBRA2	0.040/0.088

Note: The ZBRN2 has an embedded communication port for Modbus Serial Line, whereas the ZBRN1 must be plugged with a communication module to support different protocols.

Compatibility

Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2













ZB5RTA4







ZB5RTC2

Transmitter components for w	ireless and batteryless push	outtons		
Description	Type of push	Color	Reference	Weight kg/ <i>lb</i>
Fransmitter for wireless and patteryless pushbutton (1) (2)	1 radio frame sent when butto is pushed	on –	ZBRT1	0.025/0.05
	1 radio frame sent when butto is pushed 1 radio frame sent when butto is released		ZBRT2 (5)	0.025/0.05
Spring return pushbutton neads for ZBRT1 transmitter	Flush (plastic)	Without cap (3)	ZB5RZA0	0.015/0.03
	Flush (metal)	Without cap (3)	ZB4RZA0	0.030/0.06
Spring return mushroom head or ZBRT1 transmitter	Mushroom 40 mm/ <i>1.58 in.</i> (plastic)	Black	ZB5RZC2	0.025/0.05
Wireless and batteryless bushbutton including: a transmitter equipped with ixing collar a spring return mushroom nead	Mushroom 40 mm/ <i>1.58 in.</i> (plastic)	Black	ZB5RTC2	0.055/0.12
Vireless and batteryless oushbuttons including:	Flush (plastic)	White	ZB5RTA1	0.045/0.09
a transmitter equipped with ixing collar a spring return pushbutton		Black	ZB5RTA2	0.045/0.09
nead with cap attached (4)		Green	ZB5RTA3	0.045/0.09
		White I on green background	ZB5RTA331	0.045/0.09
		Red	ZB5RTA4	0.045/0.09
		White O on red background	ZB5RTA432	0.045/0.09
		Yellow	ZB5RTA5	0.045/0.09
		Blue	ZB5RTA6	0.045/0.09
	Flush (metal)	White	ZB4RTA1	0.085/0.18
		Black	ZB4RTA2	0.085/0.18
		Green	ZB4RTA3	0.085/0.18
		White I on green background	ZB4RTA331	0.085/0.18
		Red	ZB4RTA4	0.085/0.18
		White O on red background	ZB4RTA432	0.085/0.18
		Yellow	ZB4RTA5	0.085/0.18
		Blue	ZB4RTA6	0.085/0.18

(1) Fixing collar ZB5AZ009 (plastic) or ZB4BZ009 (metal) to be ordered separately.

(2) Only heads ZB4RZA0 and ZB5RZA0 are mechanically compatible.

(3) Cap to be ordered separately. Refer to the "Accessories" table on page 2/8.

(4) This cap is factory-assembled and cannot be removed (risk of damage).

(5) This transmitter is only compatible with receiver ZBRR● version ≥ 2.0, relay antenna ZBRA1 version ≥ 2.0, and Harmony Hub ZBRN• version > 1.2.

3

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2

4	Harmony Hub ecos	ystem device (continued)		
	Transmitter components for	r wireless and batteryless rope pull switch		
	Description	Application	Reference	
zdynikler ZBRP1	Rope pull switch with wireless and batteryless transmitter	For automatic doors: The rope pull switch sends a radio message to the receiver in the control panel to open and close the door.	ZBRP1	
	Rope pull switch with wireless and batteryless transmitter and a universal support accessory ZBRAUS2	For automatic doors: The rope pull switch sends a radio message to the receiver in the control panel to open and close the door.	XB5RP1US2	
XB5RP1US2				

XB4-5R_CP19264C

PF100755A

XB4-5R_60642_CPFJR17003A



Configurable receiver for l	Harmony Hub				
Description	Output function	Output type	Receiver voltage V	Reference	Weight kg/ <i>lb</i>
Wireless Receiver for Harmony Hub, 2 pusbuttons and 6 LEDs	Bistable	4 PNP outputs	24	ZBRRH	0.130/ <i>0.287</i>

Weight kg/lb 0.150/0.331

0.259/0.571

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2

	ZBA7235
	ZBA7331
3	DF569178

F54058 (\mathbf{I})



ZBA7432

Accessories - Caps for Harmony pushbutton heads ZB5RZA0 and ZB4RZA0							
Description	Background color	Marking	Sold in lots of	Unit reference	Weight kg//k		
Sets of 10 different colored caps with identical marking	White	-	10	ZBA71	0.010/0.022		
(1)		"I" (black)	10	ZBA7131	0.010/0.022		
		" 1 " (black)	10	ZBA7134	0.010/0.022		
		"+" (black)	10	ZBA7138	0.010/0.022		
	Black	-	10	ZBA72	0.010/0.022		
		"O" (white)	10	ZBA7232	0.010/0.022		
		"+" (white)	10	ZBA7233	0.010/0.022		
		"↓" (white)	10	ZBA7235	0.010/0.022		
		"I" (white)	10	ZBA7237	0.010/0.022		
	Green	-	10	ZBA73	0.010/0.022		
		"I" (white)	10	ZBA7331	0.010/0.022		
		"+" (white)	10	ZBA7333	0.010/0.022		
		" " white	10	ZBA7335	0.010/0.022		
		"II" (white)	10	ZBA7336	0.010/0.022		
	Red	-	10	ZBA74	0.010/0.022		
		"O" (white)	10	ZBA7432	0.010/0.022		
	Yellow	-	10	ZBA75	0.010/0.022		
	Blue -		10	ZBA76	0.010/0.022		
Set of 10 different colored caps with different markings (1)	White, black, green, red, ye white "I" on green backgrou background, white "O" on r white "O" on black backgro	und, black "l" on white ed background,	1	ZBA79	0.010/0.022		
Set of 6 different colored cap	s White, black, green, red, ye	ellow, blue	1	ZBA80	0.010/0.022		

(1) Cap can be clipped on at 90° steps, through 360°.

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2

	· · · · ·	Boxes for wireless and batteryless				
Straditor	Product	Application	Description	Sold in lots of	Unit reference	Weight kg/ <i>lb</i>
No.	Plastic empty mobile box	For mobile and static applications with wireless and batteryless	1 cut-out	1	ZBRM21	0.109/0.240
PF 13210		pushbuttons	2 cut-outs	1	ZBRM22	0.110/0.243
	Plastic mobile box equipped with button(s) and transmitter(s), 1 set of caps			1	ZBRM21A0	0.150/0.331
		pushbuttons	1 button with ZBRT2 transmitter	1	ZBRM21B0	0.151/0.333
BRM22 ZBRA	CS		2 buttons with 2x ZBRT1 transmitters	1	ZBRM22A0	0.194/0.428
			2 buttons with 2x ZBRT2 transmitters	1	ZBRM22B0	0.195/0.430
e-factor			1 button with ZBRT1 and 1 button with ZBRT2	1	ZBRM22AB0	0.195/0.430
0			1 button with ZBRT2 and 1 button with ZBRT1	1	ZBRM22BA0	0.195/0.430
		Special support for tube or wall for ZBRM21 and ZBRM22	r -	1	ZBRACS	0.064/0.141
BRM22A0	Empty plastic boxes for wireless and batteryless	For static or on-board wireless and batteryless pushbuttons	1 cut-out	1	XALD01	0.136/0.300
d.	pushbuttons (2)		2 cut-outs	1	XALD02	0.193/0.426
0 0	Other accessories					
	Relay antenna (3)	Between transmitter and receiver Used to increase the range and/or get round obstacles	24240 V \eqsim 15 m/16.4 ft cable 1 power-ON LED 2 LEDs (reception/transmission)	1	ZBRA1	0.200/0.441
ALDO2	Passive antenna	Passive antenna to pass through a wall, must be close to a relay antenna or a receiver	□ 2 antennas □ 0.9 m/2.95 ft cable □ 2 RF connectors	1	ZBRA3	0.010/0.328
	Vertical or horizontal support	Universal support for rope pull switch	A carabiner and a support to attach horizontally or vertically	1	ZBRAUS2	0.109/0.240
	Fixing collar	-	Plastic	10	ZB5AZ009	0.038/0.084
			Metal	10	ZB4BZ009	0.038/0.084
BRA1	Legend plate, 27 x 8 mm/ 1.06 x 0.32 in., for engraving	For sticking onto handy box JZBRM01, ZBRM21, and ZBRM22	Self-adhesive, blank, black background	10	ZBY0101T	0.005/0.011
BRA3		contacts (no cable gland outlet). land outlets, compatible with Harmon nd ZBRT2 .	y ZB5 pushbutton heads.			
69						

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal

Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2



XC-SD_520_CPMFS18017

XC-SD_520_CPMFS18019A

XB4-5R_CP19529C

XB4-5R_60642_CPMGU19001

A9MEM1560_Image_1

LV434020

LV434022

Control and signaling units Ø 22 Harmony XB5R plastic and XB4R metal Wireless and batteryless ecosystem device Harmony Hub ZBRN1 and ZBRN2

MFS 18017	2	MFS18018A					Harmon Transmitter Reference
XC-SD_520_CPMFS18017	1W110	xC-sb_520_CPME160184	12				XCMW110
				0			XCMW102
XC-SD_520_CPMF518019A		XC-SD_520_CPMFS18024A	XG-SD_520_CPMFS18021A				XCMW115
	IW115	XCMW11	16		45		XCMW116
							XCMW145
XB4-5R_CP19529C							Transmitter
ZBRT							ZBRTT1
X64-5R_60642_CPMGU19001	ST114						A9XST114
×							Transmitte
A9MEM1560_Image_1	Schreider Arweite Arweite Arweite Arweite Arweite		A9MEM1570_Image_2	R R	School and a second sec		A9MEM1560
	REM1560		Z	MEM157	0		A9MEM1570
LV434020		Contraction of the second seco	LV434021			¢	LV434020
LV43	34020		LV43	4021			LV434021
		C.					LV434022
		•	LV434023			œ	
LV43	4022			4023	(r · · · · · · · · · · · · · · · · · · ·		LV434023
LV43	7022		LV43	4023			

Harmony	Hub ecosystem (device (continued)
Transmitter co	omponents for wireless	and batteryless imit switches
Reference	Description	Benefits
XCMW110	Metal end plunger	Miniature format products designed to fit in extremely compact areas. Reduced installation time and cost, both for new machinery and renovating existing installations. No battery replacement and no recycling costs.
XCMW102	Metal roller plunger	_ 2 linear type heads: With head for linear movement (plunger)
XCMW115	Plastic roller lever	Miniature format products designed to fit in extremely compact areas. Reduced installation time and cost, both for new machinery and renovating existing installations. No battery replacement and no recycling costs.
XCMW116	Metal roller lever	_
		3 rotary type heads: With head for rotary lever
XCMW145	Adjustable length plastic roller lever	_
Transmitter co	omponents for wireless	and batteryless temperature sensors
ZBRTT1	Temperature and humidity sensor	Wireless smart sensor for continuous environmental condition monitoring, used to measure the:
		- Temperature of the surface in contact - Relative humidity
A9XST114	Temperature sensor	For measuring the temperature of food storage and processing equipment and rooms in order to maintain the cold chain.
Transmitter co	omponents for wireless	and batteryless energy sensors
A9MEM1560	Energy monitoring sensor	Cut down on installation time with the efficient and simple PowerTag® power sensor units. Designed to reduce downtime and save on costs, they provide the ultimate in convenience and flexibility.
A9MEM1570	Energy monitoring sensor	-

V434021	LV434021
	LV434022
	LV434023

LV434020	Energy sensor component	Energy Sensor PowerTag NSX for monitoring a machine's voltage, current, and energy.
LV434021	Energy sensor component	
LV434022	Energy sensor component	
LV434023	Energy sensor component	



Control and signaling units Ø 22

Harmony XB5R plastic and XB4R metal

Wireless and batteryless pushbuttons Wireless and batteryless ecosystem devices

Product reference index

Product reference index.....page 4/2

Index

Product reference index

Α	
A9MEM1560	3/9
A9MEM1570	3/9
A9XST114	1/7
	3/9

L	
LV434020	3/9
LV434021	3/9
LV434022	3/9
LV434023	3/9

X	
XALD01	2/9
	3/7
XALD02	2/9
	3/7
XB4RFA02	2/5
XB4RFB01	2/5
XB5RFA02	2/5
XB5RFB01	2/5
XB5RMA04	2/5
XB5RMB03	2/5
XB5RP1US2	2/7
	3/5
XCKW101	3/8
XCKW102	3/8
XCKW131	3/8
XCKW133	3/8
XCKW139	3/8
XCKW141	3/8
XCKW143	3/8
XCKW149	3/8
XCKW159	3/8
XCMW102	3/9
XCMW110	3/9
XCMW115	3/9
XCMW116	3/9
XCMW145	3/9
Z	

XCIIIIV 145	5/9
Z	
ZB4BZ009	2/9 3/7
ZB4RTA1	2/6 3/4
ZB4RTA2	2/6 3/4
ZB4RTA3	2/6 3/4
ZB4RTA4	2/6 3/4
ZB4RTA5	2/6 3/4
ZB4RTA6	2/6 3/4
ZB4RTA331	2/6 3/4
ZB4RTA432	2/6 3/4
ZB4RZA0	2/6 3/4
ZB5AZ009	2/9 3/7
ZB5RTA1	2/6 3/4

ZB5RTA2	2/6 3/4	ZBRAUS
ZB5RTA3	2/6 3/4	
ZB5RTA4	2/6 3/4	ZBRCET
ZB5RTA5	2/6 3/4	ZBRM21
ZB5RTA6	2/6	ZBRM21
ZB5RTA331	3/4	ZBRM21
ZB5RTA432	3/4 2/6	ZBRM22
ZB5RTC2	3/4 2/6	ZBRM22
ZB5RZA0	3/4	ZBRM22
ZB5RZC2	3/4 2/6	ZBRM22
	3/4	
ZBA71	2/8 3/6	ZBRM22
ZBA72	2/8	ZBRN1
ZBA73	3/6 2/8	ZBRN2
	3/6	
ZBA74	2/8	ZBRP1
ZBA75	3/6	
	3/6	ZBRRA
ZBA76	2/8	ZBRRC
ZBA79	3/6 2/8	ZBRRD
	3/6	
ZBA80	2/8 3/6	ZBRT1
ZBA7131	2/8 3/6	ZBRT2
ZBA7134	2/8	ZBRTT1
ZBA7138	3/6 2/8	ZBY010 ²
	3/6	
ZBA7232	2/8 3/6	
ZBA7233	2/8	
ZBA7235	3/6 2/8	
	3/6	
ZBA7237	2/8	
ZBA7331	3/6 2/8	
	3/6	
ZBA7333	2/8 3/6	
ZBA7335	2/8	
	3/6	
ZBA7336	2/8 3/6	
ZBA7432	2/8 3/6	
ZBRA1	1/7	
	2/9 3/7	
ZBRA2	1/7	
	3/3	
ZBRA3	1/7 2/9	
	3/7	
ZBRACS	2/9	
	3/7	

ZBRAUS2	2/7
	2/9
	3/5
	3/7
ZBRCETH	1/7
	3/3
ZBRM21	2/9
	3/7
ZBRM21A0	2/9
	3/7
ZBRM21B0	2/9
	3/7
ZBRM22	2/9
	3/7
ZBRM22A0	2/9
	3/7
ZBRM22AB0	2/9
	3/7
ZBRM22B0	2/9
	3/7
ZBRM22BA0	2/9
	3/7
ZBRN1	1/7
	3/3
ZBRN2	1/7
	3/3
ZBRP1	1/7
	2/7
	3/5
ZBRRA	2/7
ZBRRC	2/7
ZBRRD	2/7
ZBRRH	1/7
	3/5
ZBRT1	2/6
	3/4
ZBRT2	2/6
	3/4
ZBRTT1	3/9
ZBY0101T	2/9
	3/7

Life Is On Schneider



Learn more about our products at <u>www.schneider-electric.com</u>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Design: Schneider Electric Photos: Schneider Electric

Schneider Electric Industries SAS Head Office 35, rue Joseph Monier - CS 30323 F-92500 Rueil-Malmaison Cedex France

DIA5ED2121214EN March 2020 - V8.0