

Product data sheet

Specifications



integrated servo motor - 1.1 Nm - 6000 rpm - without brake

ILM0701P01A0000

Main

Range of product	PacDrive 3
Product or component type	Servo motor integrated drive
Device short name	ILM

Complementary

[Us] rated supply voltage	250...700 V
Continuous stall current	1.55 A
Continuous stall torque	1.1 N.m
Peak stall torque	3.5 N.m
Nominal output power	310 W
Nominal torque	0.5 N.m
Nominal speed	6000 rpm
Maximum current Irms	5.7 A
[In] rated current	0.6 A
Shaft end	Untapped
Second shaft	Without second shaft end
Shaft diameter	11 mm
Shaft length	23 mm
Key width	18 mm
Feedback type	Absolute single turn SinCos Hiperface
Speed feedback resolution	128 periods
Holding brake	Without
Mounting support	International standard flange
Motor flange size	70 mm
Torque constant	0.71 N.m/A at 120 °C
Back emf constant	46 V/krpm at 20 °C
Number of motor poles	6
Rotor inertia	0.25 kg.cm²
Stator resistance	10.4 Ohm at 20 °C for Ph/Ph

	7.23 Ohm at 120 °C for Ph/N
Stator inductance	38.8 mH at 20 °C for Ph/Ph 19.4 mH at 120 °C for Ph/N
Maximum radial force Fr	660 N at 1000 rpm 520 N at 2000 rpm 460 N at 3000 rpm 410 N at 4000 rpm 380 N at 5000 rpm 360 N at 6000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	212 mm
Number of motor stacks	1
Centring collar diameter	60 mm
Centring collar depth	2.5 mm
Number of mounting holes	4
Mounting holes diameter	5.5 mm
Circle diameter of the mounting holes	82 mm
Net weight	2.7 kg

Environment

IP degree of protection	IP54
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.3 kg
Package 1 Height	21.0 cm
Package 1 width	18.0 cm
Package 1 Length	35.6 cm
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Weight	52.0 kg
Package 2 Height	81.0 cm
Package 2 width	60.0 cm
Package 2 Length	80.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Circularity Profile	End of Life Information
PVC free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov