LEVEL & LEAK DETECTION

POINT LEAK DETECTION SENSOR LIQUI-TECT® 410

DESCRIPTION

The Liqui-tect® 410 (LT410) provides a single-point detection of leaks. The point detection sensor has two goldplated sensing probes to prevent corrosion resistance and to provide accurate readings. The LT410 constantly monitors points for leaks, internal faults and power failures and warns of any abnormal conditions. Mouting brackets allow for sensor height adjustments and leveling.















APPLICATION

- · Glycol, chilled water cooling
- Humification feed water piping
- · Condensate pumps and drains
- Unit and ceiling auxiliary drip pans Overhead piping troughs

EVEL & LEAK DETECT


DIMENSIONS





Adjustable probe height 0.0-0.5" (0.0-12.7mm)

> Shipping weight: 2 lbs (0.9 kg) Mounting holes: #8 screws



SPECIFICATIONS

Contact Rating 2 Form-C; 3 A rating at 24 VAC **Operating Altitude** 0 to 10,000 ft (0 to 3,048 m) 10% to 95% relative humidity (non-**Operating Humidity**

condensing)

Operating Temperature 50°F to 104°F (10°C to 40°C)

Enclosure Rating

Dimensions 6.35"W x 2.25"D x 4.46"H (161.2 x 57.2 x 113.2 mm) **Power Requirements**

24 VAC 100 mA, 50/60 Hz,

3 VA (max.)

UL File #E167733, C-UL, CE, FCC **Approvals**

Compliance 2.0 lbs (0.9kg)

Weight

NEMA 1, IP 30

NEW!

LEVEL & LEAK DETECTION

POINT LEAK DETECTION SENSOR LIQUI-TECT® 410



WIRING

Power Wiring

The LT410 is rated for 24 VAC, 50/60 Hz and 0.10 amp.

Figure 1 24V from Liebert environmental units to LT410





Figure 2 24V from transformer to LT410

MODEL

LT410



Wiring to Auxiliary Alarm Panels

The LT410 has two Form-C dry contact alarm output contacts: orange wires (1) and yellow wires (2). Each contact is rated for 24 VAC at 3 amp.

Figure 3 LT410 to Liebert environmental units





Figure 4 LT410 to Liebert contact monitor panel



Wiring Interconnections

Red Wires		Ora	nge W	ires)	Yellow Wires	
24 V, AC/DC @0.10A, 50-60 Hz, DC Class 2 Circuit Only			VAC @	3A		Alarm Contact Rating 24 VAC @ 3A Class 2 Circuit Only	
Power	Power	1-NO	1-NC 1-COM	2-NO	2-NC 2-COM		
Gold		ed	<u> </u>			ht adjustable "' (0-12.7mm)	



NFWI