



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	CD with software Documentation CD Installation guide Rack mounting support rails USB cable
Product web sub-family	Lithium-Ion
Number of tare power	8 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Number of rack unit	1U
Colour	Black with silver front bezel
Depth	23.2 cm
Height	4.4 cm
Mounting support	Floor Wall
Mounting preference	No preference
Product weight	4.18 kg
Mounting mode	Rack-mounted
Two post mountable	1
USB compatible	Yes
Width	43.2 cm

Input

Network frequency	47...63 Hz
Plug standard	NEMA 5-15P
Input voltage limits	92...139 V
Input voltage	120 V

Output

Rated power in W	400 W
Maximum configurable power in W	400 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Line interactive
Wave type	Sine wave
Nb of power socket outlets	4 NEMA 5-15R
Output voltage	120 V
Maximum configurable power in VA	500 VA
Rated power in VA	500 VA
Transfer time	6 ms typical : 10 ms maximum

Conformance

Product certifications	cULus NOM
Standards	CSA C22.2 No 107.3 FCC part 15 class A UL 1778 UL 1973
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	10...90 % non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	Non-condensing 10...90 %
Storage altitude	0.00...14999.82 m
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Li-Ion (Lithium-Ion)
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Liquid value	0
Battery charger power	10 W rated
Battery design life	5...10 year(s)
Battery power in VAh	30 VAh runtime
Battery life	8...10 year(s)
Extended runtime	0

Communications & Management

Free slots	0
Control panel	LED status display with on line : on battery : replace battery and building wiring fault

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
-------	---

Surge Protection and Filtering

Surge energy rate	680 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	6 kg
Package 1 Height	16.8 cm
Package 1 width	59 cm
Package 1 Length	33.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------