# **PASxx Series**



## **MONITOR AIR DUCTS, FILTERS & FANS**

### **FEATURES**

- · Easy to install
- · User-friendly snap cover
- · Case geometry allows easy cable lead-in
- Cable strain relief integrated in PG11 (DIN 40430)
- High adjustment accuracy through individual laser etched scale
- Long-term stability of switching points through trapezoidal bead diaphragm
- Multi-layer gold plated contact

### **DESCRIPTION**

This series of four PASxx differential air flow switches are intended for use in air handling systems for the monitoring of air ducts, filters and fans.

The enclosure is plastic with a rating of IP54. A set-point adjustment is provided under the clip-on clear plastic cover.

Supplied complete with mounting adaptor ring, two straight duct probes and a 6-foot length of clear tubing.

## **APPLICATIONS**


- · High pressure monitoring
- · Vacuum pressure monitoring
- · Filter monitoring
- · Fan monitoring


### **SPECIFICATIONS**


Medium		Air and neutral gases
Pressure range		See Ordering Information table
Set-point scale		Inches WC
Tolerable overload on one side		20 in. WC at -22 to +185 °F
Repeatability	PAS01	±2.5 (0.01 in. WC)
	PAS02	±5 (0.02 in. WC)
	PAS03	±5 (0.02 in. WC)
	PAS04	±5 (0.02 in. WC)
Switching load	Resistive load	5 A at 250 Vac 4 A at 30 Vdc
	Inductive	0.8 A at 250 Vac 0.7 A at 30 Vdc
Materials in contact with the medium		Case: PC 10% GF Cover: PC Diaphragm: Silicone LSR tempered 200 °C, free of gas emissions
Operating temperature	Medium/ambient	-22 to +185 °F (-30 to +85 °C)
	Storage	-40 to +185 °F (-40 to +85 °C)
Service life		Mechanical > 106 switching cycles
Electrical connection		Screw terminals Cable gland type PG11 (DIN 40430) complete with cable strain relief
Switch contact type		SPDT (change-over)
Protection standard	Without cover	IP00
	With cover	IP54
Pressure connections		Pipe Ø 6.2 mm
Tests/admissions		EU Conformity: Electromagnetic Compatibility: CE¹ conformity according to EN 60730-2-6:2008 Low Voltage Directive: 2014/35/EU Gas Appliance Directive: 2009/142/EC Pressure Sensing Devices for Gas Burners and Gas Burning Appliances: EN 1854:2010 EU Directive on RoHS: 2011/65/EU


<sup>1.</sup> The CE mark indicates RoHS2 compliance. Please refer to the CE Declaration of Conformity for additional details.


## **DIMENSIONAL DRAWING**











#### **FUNCTIONALITY**

The pressure switch has two separate pressure chambers, each with its own connection. The switch operates when the setpoint is either exceeded or not reached.

#### **Vacuum Monitoring**

Connect the pressure switch via P2. Do not connect P1. Leave P1 open. Make sure that dirt cannot get into P1.

#### **High Pressure Monitoring**

Connect the pressure switch via Pa. Do not Connect P2. Leave P2 open. Make sure that dirt cannot get into P2.

#### **Filter Monitoring**

Connect P1 before the filter and P2 after it.

#### **Fan Monitoring**

Connect P1 after the fan (in blowing direction) and P2 before the fan.

## **ORDERING INFORMATION**



PART NUMBER	DESCRIPTION	PRESSURE RANGE
PAS01	Differential Air Pressure Switch	0.08 to 1.2 in. WC (20 to 300 Pa)
PAS02	Differential Air Pressure Switch	0.2 to 2.0 in. WC (50 to 500 Pa)
PAS03	Differential Air Pressure Switch	0.4 to 4.0 in. WC (100 to 1000 Pa)
PAS04	Differential Air Pressure Switch	2.0 to 8.0 in. WC (500 to 2000 Pa)

