



Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007CS9 9007T10S9 9007NS9 9007AS9 9007BS9 9007T5S9
Associated complete product	9007FT 9007T 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 63.50 mm - offset: - convertible roller
Type of roller	1 steel outside roller (convertible) diameter: 25.40 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-23...85 °C
Ambient air temperature for storage	-23...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	104.326 g
Package 1 Height	2.032 cm
Package 1 width	2.54 cm
Package 1 Length	8.89 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------