



## Main

Range of product	Modicon M340 automation platform
Product or component type	Analog output module
Electrical connection	1 connector 20 ways
Input output isolation	Non isolated

## Complementary

Measurement error	$\leq 0.25\%$ of full scale $0...60\text{ }^{\circ}\text{C}$ $0.1\%$ of full scale $25\text{ }^{\circ}\text{C}$
Temperature drift	$45\text{ ppm}/^{\circ}\text{C}$ $0...20\text{ mA}$ $45\text{ ppm}/^{\circ}\text{C}$ $4...20\text{ mA}$
Common mode between channels	$\geq 80\text{ dB}$
Isolation voltage	$1400\text{ V DC}$ between channels and ground $1400\text{ V DC}$ between channels and bus
Detection type	Open circuit $4...20\text{ mA}$ Short circuit $0...20\text{ mA}$
Load impedance ohmic	$\leq 350\text{ Ohm}$ $0...20\text{ mA}$ $\leq 350\text{ Ohm}$ $4...20\text{ mA}$
Output level	High level
Analogue output number	8
Analogue output type	Current $0...20\text{ mA}$ Current $4...20\text{ mA}$
Analogue output resolution	15 bits + sign
Supply	Internal power supply via rack
Conversion time	$\leq 4\text{ ms}$
Maximum conversion value	$0...21\text{ mA}$ $0...20\text{ mA}$ $0...21\text{ mA}$ $4...20\text{ mA}$
Fallback mode	Configurable Predefined
Status LED	1 LED green RUN 1 LED per channel green channel diagnostic 1 LED red ERR 1 LED red I/O

Product weight	0.15 kg
Current consumption	150 mA at 3.3 V DC 74 mA at 24 V DC

## Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % without condensation
IP degree of protection	IP20
Protective treatment	TC

## Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0901 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Available <a href="#">End of life manual</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Modules Mounted on Racks


Dimensions



- (1) With removable terminal block (cage, screw or spring).
- (2) With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81

## Wiring Diagram



Ix + pole input for channel x.

COMx pole input for channel x, COMx are connected together internally.

The current loop is self-powered by the output and does not request any external supply.