# BMXCPS3020

power supply module X80 - 24..48 V DC - 31.2 W



Main		
Range of product	Modicon M340 automation platform	
Product or component type	Power supply module	
Backplane compatibility	Not compatible with BMEXBP02	
Primary voltage	2448 V isolated	
Supply circuit type	DC	
Total useful secondary power	<= 31.2 W	
Secondary power	31.2 W 24 V DC I/O module power supply and processor	

#### Complementary

Primary voltage limit	1862.4 V	
Power supply input current	1.65 A 24 V 0.83 A 48 V	
Inrush current	60 A 48 V 30 A 24 V	
I <sup>2</sup> t on activation	<= 3 A <sup>2</sup> .s 48 V <= 1 A <sup>2</sup> .s 24 V	
It on activation	<= 0.3 A.s 48 V <= 0.2 A.s 24 V	
Protection type	Short-circuit protection secondary circuit, 24 V sensor power supply Overvoltage protection secondary circuit, 24 V sensor power supply Overload protection secondary circuit, 24 V sensor power supply Internal fuse not accessible primary circuit	
Current at secondary voltage	4.5 A 3.3 V DC I/O module logic power supply 1.3 A 24 V DC I/O module power supply and processor	
Power dissipation in W	<= 8.5 W	
Status LED	1 LED green rack voltage OK	
Control type	RESET push-button cold restart	
Electrical connection	1 connector 5 pin(s) line supply, protective earth 1 connector 2 pin(s) alarm relay	
Cable length	15 m power supply cable copper 2.5 mm <sup>2</sup> 10 m power supply cable copper 1.5 mm <sup>2</sup>	
Insulation resistance	>= 10 mOhm primary/secondary >= 10 mOhm primary/ground	
Product weight	0.34 kg	

#### Environment

Immunity to microbreaks	<= 1 ms	
Dielectric strength	1500 V primary/secondary 1500 V primary/ground	
IP degree of protection	IP20	
Standards	IACS E10	
Ambient air temperature for storage	-4085 °C	
Ambient air temperature for operation	060 °C	
Relative humidity	1095 % without condensation	
Protective treatment	TC	

#### Offer Sustainability

Sustainable offer status	Not Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0722 - Schneider Electric declaration of conformity	
REACh	Reference contains SVHC above the threshold - 🗗 go to CaP for more details	
Product environmental profile	Available Download Product Environmental	




## Product data sheet **Dimensions Drawings**

## BMXCPS3020

#### Modules Mounted on Racks

#### **Dimensions**




- With removable terminal block (cage, screw or spring). With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81

### BMXCPS3020


#### Connection of Direct Current Power Supply Modules to a 24 Vdc or 48 Vdc Floating Direct Current Network



24 VDC floating network for the power supply of sensors, actuators and input/out modules.


Connection of Direct Current Power Supply Modules to an Alternating Current Network

#### Connection of a Single Rack PLC Station



- Q General isolator
- KM Line contactor or circuit breaker
- (1) Insulation connector bar for locating grounding errors

#### Connection of a Multi-Rack PLC Station



- Q General isolator
- KM Line contactor or circuit breaker
- (1) Insulation connector bar for locating grounding errors