

Product data sheet

Characteristics

9002AW11

Foot Switch, Harmony, industrial, unshielded, maintained contact, 3A at 230 VAC, SPST contact, NEMA 2, 4, 13 enclosure

Product availability : Stock - Normally stocked in distribution facility



Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPST
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Maintained

Ordering and shipping details

Category	"21441 - 9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	00785901816737
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	3.50 in (8.890 cm)
Package 1 width	5.00 in (12.700 cm)

Package 1 Length	9.30 in (23.622 cm)
------------------	---------------------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------