

Product data sheet

Characteristics

EXN75T3H

DOE 2016 LV XFMR, 3 Phase, 75kVA, 480
Delta-208Y/120, AL, 150C Rise

Product availability : Stock - Normally stocked in distribution facility



Price** : 4,744.00 USD



Main

Range of product	Square D
Product or component type	DOE 2016 energy efficient transformer
Device application	Low voltage electrical distribution

Complementary

Box number	20M
Phase	Three phase
Rated operational power in VA	75 kVA
Network frequency	60 Hz
Type of cooling	Natural convection
Primary voltage	480 V delta
Number of tap-offs	2 2.5 % FCAN 4 2.5 % FCBN
Primary operational current	208.18 A
Secondary voltage	208Y/120 V
Coil Material	Aluminium
Basic IMP level (BIL)	10 kV
Temperature Rating	150 °C 220 °C insulated
DOE Efficiency	98.63 % at 35 % load factor , 167 °F (75.0 °C)
Sound Level	3 dB NEMA ST-20 47 dB
%IZ	4.90 %
%IX	3.97 %
X/R Ratio	1.54
Inrush current	985 A
Let Through Current	3.71 kA

Transformer Losses	142 no load (core loss) 2226 load loss (coil loss)
Transformer BTU/HR	696 16.6 % 959 25 % 2383 50 % 4757 75 % 8080 100 %
Height	33.50 in (851 mm)
Depth	27.44 in (697 mm)
Width	30.08 in (764 mm)
Net weight	515.00 lb(US) (233.60 kg)
Mounting support	Floor Floor, with 7400FMB Ceiling, with 7400CMB18M19M20M Wall, with 7400WMB18M19M20M
Degree of protection	UL type 2 UL type 3R, with 7400WS18M19M20M
Electrical connection	2 Hole Nema Pad primary 0.44 in (11.1 mm) 2 Hole Nema Pad secondary 0.44 in (11.1 mm) 4 Hole Nema Pad sec - XO 0.44 in (11.1 mm)
Number of mounting holes	0.51 in (13 mm)

Environment

Ambient air temperature for operation	104 °F (40 °C)
Average ambient air temperature for operation	30 °C
Standards	UL 1561 CSA C22.2 No 47 NEMA ST-20

Ordering and shipping details

Category	16256 - 3PH EXN/2016 15-150KVA LVGP XFMR
Discount Schedule	PE2X
GTIN	00785901272687
Package weight(Lbs)	281.23 kg (620 lb(US))
Returnability	Yes
Country of origin	MX