



## Overview

Description	APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Model Name	Rack PDU 2G, Switched, ZeroU, 20A, 100-120V, (24) 5-20R
Includes	Installation guide , Rack Mounting brackets , Safety guide , Serial configuration cable
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

## Output

Nominal Output Voltage	120V
Output Connections	(24) NEMA 5-20R (Battery Backup)

## Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	16 A
Input Connections	NEMA L5-20P
Cord Length	3 meters
Number of Power Cords	1
Acceptable Input Voltage	100-120 VAC
Maximum Input Current per phase	20 A
Load Capacity	1920 VA

## Physical

Net Weight	6.52 kg
------------	---------

Maximum Height	1791.0 mm
Maximum Width	55.0 mm
Maximum Depth	46.0 mm
Shipping Weight	8.6 kg
Shipping Height	2006.0 mm
Shipping Width	165.0 mm
Shipping Depth	109.0 mm
Color	Black

## Environmental

Operating Environment	-5 - 45 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	FCC Part 15 Class A , ICES-003 , UL 60950-1 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant