

Product data sheet

Characteristics

EZMH115125

MTR EZMH BRANCH RINGLESS 125A QO HORN

Product availability : Stock - Normally stocked in distribution facility



Price** : 2,910.00 USD



Main

| | |
|-------------------------|--------------------------|
| Product | Meter Center Branch Unit |
| Current Rating | 125 A |
| Type | Meter-Pak |
| Bus Rating | 800 A |
| Number of Jaws | 5 without jaw release |
| Number of Meter Sockets | 5 |
| Bypass Type | Horn bypass |
| Socket Type | Ringless |

Complementary

| | |
|------------------------|---------------------------|
| Certifications | UL listed |
| Busbar Material | Aluminium busbar |
| Enclosure Material | Steel |
| Enclosure Rating | NEMA 3R |
| Maximum Voltage Rating | 120/240 V AC |
| Mounting | Surface |
| Phase | 1 phase in 1 phase out |
| Wire Configuration | 3-wire |
| Height | 1450.85 mm (57.12 in) |
| Width | 311.15 mm (12.25 in) |
| Depth | 180.09 mm (7.09 in) |

Ordering and shipping details

| | |
|-------------------|----------------------|
| Category | 00020 - EZ METER-PAK |
| Discount Schedule | DE4 |

| | |
|---------------------|-------------------------|
| GTIN | 00785901402312 |
| Package weight(Lbs) | 34.34 kg (75.71 lb(US)) |
| Returnability | Yes |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.For more information go to www.p65warnings.ca.gov |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|