



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LR3D01...D35 LR3D313...LR3D365 LRD01...35 LRD313...LRD365
[Uc] control circuit voltage	110 V AC 50/60 Hz 110 V DC

Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	108 g
Package 1 Height	4.8 cm
Package 1 width	4.8 cm
Package 1 Length	5.2 cm
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Weight	3.643 kg
Package 2 Height	15 cm
Package 2 width	15 cm

Package 2 Length	40 cm
------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------