

# Product data sheet

## Characteristics

# M9F43203

## Multi 9 - C60BP - MCB - 2P - 3 A - D Curve - 480Y/277 V - 10 kA - UL 489

Product availability : Stock - Normally stocked in distribution facility



Price\* : 269.00 USD



### Main

|                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|---------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                     | Multi 9                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Product name              | Multi 9 C60                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Product or component type | Miniature circuit-breaker                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Device short name         | C60BP                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Device application        | Distribution                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Poles description         | 2P                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Number of protected poles | 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| [In] rated current        | 3 A at 77 °F (25 °C) conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Network type              | AC<br>DC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Trip unit technology      | Thermal-magnetic                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Curve code                | D                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Breaking capacity         | Icu 6 kA at 440 V AC conforming to EN/IEC 60947-2<br>Icu 10 kA at 415 V AC conforming to EN/IEC 60947-2<br>Icu 20 kA at 240 V AC conforming to EN/IEC 60947-2<br>Icu 6 kA at 440 V AC conforming to GB 14048.2<br>Icu 10 kA at 415 V AC conforming to GB 14048.2<br>Icu 20 kA at 240 V AC conforming to GB 14048.2<br>AIR 14 kA at 240 V AC conforming to UL 489<br>AIR 10 kA at 125 V DC conforming to UL 489<br>AIR 10 kA at 480Y/277 V AC conforming to UL 489<br>AIR 14 kA at 240 V AC conforming to CSA C22.2 No 5<br>AIR 10 kA at 480Y/277 V AC conforming to CSA C22.2 No 5<br>AIR 10 kA at 125 V DC conforming to CSA C22.2 No 5 |
| Suitability for isolation | Yes conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Standards                 | UL 489<br>CSA C22.2 No 5<br>GB 14048.2<br>EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Product certifications    | UL<br>CSA                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |

## Complementary

|                                        |                                                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| System Voltage                         | 240 V AC 50/60 Hz<br>415 V AC 50/60 Hz<br>440 V AC 50/60 Hz                                                                                                                                                                                                                                                                                                                                            |
| Magnetic tripping limit                | 12 x In +/- 20% AC<br>17 x In +/- 20% DC                                                                                                                                                                                                                                                                                                                                                               |
| [Ics] rated service breaking capacity  | 4.5 kA 75 % x Icu at 440 V AC conforming to EN/IEC 60947-2<br>7.5 kA 75 % x Icu at 415 V AC conforming to EN/IEC 60947-2<br>15 kA 75 % x Icu at 240 V AC conforming to EN/IEC 60947-2<br>4.5 kA 75 % x Icu at 440 V AC conforming to GB 14048.2<br>7.5 kA 75 % x Icu at 415 V AC conforming to GB 14048.2<br>15 kA 75 % x Icu at 240 V AC conforming to GB 14048.2                                     |
| [Ui] rated insulation voltage          | 500 V AC conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                      |
| Contact position indicator             | Yes                                                                                                                                                                                                                                                                                                                                                                                                    |
| Control type                           | Toggle                                                                                                                                                                                                                                                                                                                                                                                                 |
| Local signalling                       | ON/OFF indication                                                                                                                                                                                                                                                                                                                                                                                      |
| Mounting mode                          | Clip-on                                                                                                                                                                                                                                                                                                                                                                                                |
| Mounting support                       | DIN rail                                                                                                                                                                                                                                                                                                                                                                                               |
| 9 mm pitches                           | 4                                                                                                                                                                                                                                                                                                                                                                                                      |
| Height                                 | 4.06 in (103 mm)                                                                                                                                                                                                                                                                                                                                                                                       |
| Width                                  | 1.42 in (36 mm)                                                                                                                                                                                                                                                                                                                                                                                        |
| Depth                                  | 2.83 in (72 mm)                                                                                                                                                                                                                                                                                                                                                                                        |
| Colour                                 | Grey                                                                                                                                                                                                                                                                                                                                                                                                   |
| Mechanical durability                  | 20000 cycles                                                                                                                                                                                                                                                                                                                                                                                           |
| Electrical durability                  | 10000 cycles                                                                                                                                                                                                                                                                                                                                                                                           |
| Provision for padlocking               | Padlockable                                                                                                                                                                                                                                                                                                                                                                                            |
| Connections - terminals                | Tunnel type terminal, top or bottom flexible with ferrule wire(s) 0...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) max (AWG 18...AWG 8)<br>Tunnel type terminal, top or bottom rigid wire(s) 0...0.04 in <sup>2</sup> (1...25 mm <sup>2</sup> ) max (AWG 18...AWG 8)<br>Tunnel type terminal, top or bottom flexible wire(s) 0...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) max (AWG 18...AWG 8) |
| Wire stripping length                  | 0.55 in (14 mm) (top or bottom)                                                                                                                                                                                                                                                                                                                                                                        |
| Tightening torque                      | 22.12 lbf.in (2.5 N.m) (top or bottom)                                                                                                                                                                                                                                                                                                                                                                 |
| Earth-leakage protection               | Without                                                                                                                                                                                                                                                                                                                                                                                                |

## Environment

|                                       |                                                                                |
|---------------------------------------|--------------------------------------------------------------------------------|
| IP degree of protection               | IP40 modular enclosure conforming to IEC 60529<br>IP20 conforming to IEC 60529 |
| Pollution degree                      | 3 conforming to EN/IEC 60947-2                                                 |
| Tropicalisation                       | 2 conforming to IEC 60068-1                                                    |
| Relative humidity                     | 95 % ( 131 °F (55 °C) )                                                        |
| Operating altitude                    | 0...6561.68 ft (0...2000 m)                                                    |
| Ambient air temperature for operation | -22...158 °F (-30...70 °C)                                                     |
| Ambient air temperature for storage   | -40...176 °F (-40...80 °C)                                                     |

## Ordering and shipping details

|                       |                           |
|-----------------------|---------------------------|
| Category              | 00949 - M9 GEN 2 CB UL489 |
| Discount Schedule     | DE2                       |
| GTIN                  | 00785901694618            |
| Nbr. of units in pkg. | 1                         |
| Package weight(Lbs)   | 0.5400000000000004        |
| Returnability         | Y                         |
| Country of origin     | FR                        |

## Offer Sustainability

|                                  |                                                                                                                                                                                                                         |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                                                                                                   |
| RoHS (date code: YYWW)           | Compliant - since 1719 - Schneider Electric declaration of conformity<br> <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                                                                                                  |
| Product environmental profile    | Available                                                                                                                                                                                                               |
| Product end of life instructions | Need no specific recycling operations                                                                                                                                                                                   |