

Product data sheet

Characteristics

NSYCVF300M115PF

ClimaSys forced vent. IP54, 300m³/h, 115V, with outlet grille and filter G2



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 300 m ³ /h at 50 Hz Free flow rate with standard filter: 350 m ³ /h at 60 Hz
[Us] rated supply voltage	75...126 V
Input voltage	115 V 50/60 Hz

Complementary

Absorbed power	36 W 50 Hz 36 W 60 Hz
[In] rated current	0.35 A 50 Hz 0.32 A 60 Hz
Noise level < at	55...56 dB
Bearing type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External: 116 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.3 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m ³ /h
Connections - terminals	Faston connector
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template 1 power cord

Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software
------------------	---

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
