



### Main

|                           |  |
|---------------------------|--|
| Range of product          | Harmony XVB Universal  |
| Product or component type | Base unit with cover   |
| Component name            | XVBC   |
| Material                  | Glass reinforced polyamide base unit<br>Polycarbonate cover unit |

### Complementary

|                               |  |
|-------------------------------|--|
| Fixing mode                   | Direct or tube fixing  |
| Mounting diameter             | 70 mm  |
| Product destination           | Banks without flash discharge tube unit                                      |
| Electrical connection         | 1 connector for standard input   |
| Cable entry                   | Bottom or side entry   |
| Assembly style                | Customer assembly, up to 5 units   |
| Terminals description ISO n°1 | (COM-1)PW<br>(COM-2)PW<br>(COM-3)PW<br>(COM-4)PW<br>(COM-5)PW<br>(GND)GROUND |
| Product weight                | 0.19 kg  |

### Environment

|                                     |  |
|-------------------------------------|--|
| Product certifications              | CCC<br>CSA C22-2 No 14<br>GOST<br>UL 508 |
| Standards                           | EN/IEC 60947-5-1                         |
| Protective treatment                | TC                                       |
| Ambient air temperature for storage | -40...70 °C                              |
| NEMA degree of protection           | NEMA 4X indoor UL 508                    |

Contractual warranty

---


|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---

Indicator Bank without “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) Cover (supplied with base unit)


| Number of illuminated or audible signalling units (no “flash”) | b in mm | b in in. |
|--|---------|----------|
| 1  | 138     | 5.43     |
| 2  | 201     | 7.91     |
| 3  | 264     | 10.39    |
| 4  | 327     | 12.87    |
| 5  | 390     | 15.35    |

---

Base Unit for Indicator Banks

---

Panel Cut-out for Direct Fixing



---

Illuminated Beacon

---

Wiring Diagram

