

Product availability : Stock - Normally stocked in distribution facility



Price\* : 485.00 USD



### Main

|                      |                        |
|----------------------|------------------------|
| Marketing Trade Name | QO                     |
| Product              | Load Center            |
| Enclosure type       | Weatherproof enclosure |
| Cover type           | Surface cover          |

### Complementary

|                                        |                                                       |
|----------------------------------------|-------------------------------------------------------|
| Tightening torque                      | Main lugs 50 lb.in, AWG 6...AWG 2/0, aluminium/copper |
| Load Center Type                       | Main lugs                                             |
| Line Rated Current                     | 125 A                                                 |
| Number of spaces                       | 12                                                    |
| Max Short Circuit Current Rating       | 65 kA                                                 |
| Maximum Number of Single Pole Circuits | 12                                                    |
| Maximum Number of Tandem Breakers      | 0                                                     |
| Number of Phases                       | 3 phase                                               |
| Voltage Rating                         | 208Y/120 V AC<br>240/120 V delta AC<br>240 V delta AC |
| Wire Size                              | AWG 6...AWG 2/0 aluminium/copper                      |
| Electrical Connection                  | Lugs                                                  |
| Grounding Bar                          | Grounding bar included (not installed)                |
| Electrical connection                  | Lugs                                                  |
| Wiring configuration                   | 4-wire<br>3-wire                                      |
| Busbar Material                        | Tin plated copper busbar                              |
| Enclosure Material                     | Welded galvanized steel                               |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|                |                   |
|----------------|-------------------|
| Cover Finish   | Baked enamel Gray |
| Box number     | 3R                |
| Maximum Height | 18.94 in (481 mm) |
| Maximum Width  | 14.76 in (375 mm) |

## Environment

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Enclosure Rating                      | NEMA 3R outdoor                 |
| Ambient air temperature for operation | 23 °F (-5 °C)<br>104 °F (40 °C) |
| Product certifications                | UL Listed                       |

## Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 00017 - QO 3PH LOAD CENTER,OUTDOOR |
| Discount Schedule     | DE3                                |
| GTIN                  | 00785901295044                     |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 21.52 lb(US) (9.76 kg)             |
| Returnability         | Yes                                |
| Country of origin     | US                                 |

## Packing Units

|                              |                            |
|------------------------------|----------------------------|
| Unit Type of Package 1       | PCE                        |
| Package 1 Height             | 20.60 in (52.324 cm)       |
| Package 1 width              | 4.90 in (12.446 cm)        |
| Package 1 Length             | 15.70 in (39.878 cm)       |
| Unit Type of Package 2       | PAL                        |
| Number of Units in Package 2 | 39                         |
| Package 2 Weight             | 840.00 lb(US) (381.017 kg) |
| Package 2 Height             | 40.00 in (101.6 cm)        |
| Package 2 width              | 40.00 in (101.6 cm)        |
| Package 2 Length             | 48.00 in (121.92 cm)       |

## Offer Sustainability

|                            |                                                                                                             |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                           |
| REACH free of SVHC         | Yes                                                                                                         |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>                                                            |
| Toxic heavy metal free     | Yes                                                                                                         |
| Mercury free               | Yes                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|