



TEMPERATURE

AVERAGING THERMISTOR SENSOR

ST-FZ* SERIES



DESCRIPTION

The Precon **ST-FZ* Series Averaging Thermistor Sensor** provides precision remote temperature sensing for building automation systems and mechanical equipment room instrumentation. The active sensing elements are constructed of highly stable precision thermistor materials accurate to within $\pm 0.36^{\circ}\text{F}$ (0.2°C).

The sensing elements are sealed in a $3/16"$ (0.48 cm) soft-drawn copper-coiled tube attached to a standard handy box with mounting bracket attached.

FEATURES

- **Lifetime warranty**
- **$\pm 0.36^{\circ}\text{F}$ ($\pm 0.2^{\circ}\text{C}$) accuracy**
- **Wide selection of thermistor curves**
- **Adaptable to most duct sizes**
- **Easy to mount to duct wall**
- **$3/16"$ (0.48 cm) soft copper sensor**
- **Copper facilitates quick average temperature response**

OPTIONS

- **8' (2.4m) long element for very small ducts**
- **12.5' (3.8m) long element for small ducts**
- **25' (7.6m) long element for larger ducts**
- **Weather resistant handy box**



ST-FZ*



APPLICATION

The **ST-FZ* Series** is designed for direct mounting to sheet metal for average duct temperature sensing. The sensor is multipoint sensitive through the length of the temperature conductive tubing. The 8' (2.4m) and 12.5' (3.8m) models contain four sensing elements, and the 25' (7.6m) model has nine sensing elements. The thermistors are configured in a series/parallel method, which creates an end result of total average resistance, equal to the same span as a standard thermistor, with a temperature range of 32° to 160°F (0° to 71°C).

SPECIFICATIONS

Accuracy	$\pm 0.36^{\circ}\text{F}$ (0.2°C)	Heat dissipation	2.7 mW/ $^{\circ}\text{C}$ (power needed to raise the temperature by 1°C)
Sensor types		Connections	8' (2.4m) of 24 AWG, pigtails prestripped
Thermistor @ 77°F	2.252 k Ω , 3 k Ω , 10 k Ω , 20 k Ω , 100 k Ω	Mounting	Directly to duct with back box, clips available for serpentine mounting
Temperature range	32° to 160°F (0° to 71°C)	Warranty	Lifetime
Temperature response	Negative temperature coefficient		
Stability	0.24°F (0.13°C) over five years		

TEMPERATURE

AVERAGING THERMISTOR SENSOR

ST-FZ* SERIES




TEMPERATURE


MOUNTING / WIRING

Mounting

Drill a 5/8" (1.6 cm) hole for probe insertion and serpentine the sensor across the duct, turning at each end using the Model M-648 end clip and Model M-633 mid-duct support. Avoid kinking the tube as this could cause a short circuit. Using the provided #6 screws, secure the box to the duct either with the mounting ears or through the box holes.



DIMENSIONS



ORDERING INFORMATION

MODEL	DESCRIPTION
ST-FZ3	10,000Ω averaging thermistor @ 77°F (25°C), Type III (gray leads)
ST-FZ21	2252Ω averaging thermistor @ 77°F (25°C), Type II (green leads)
ST-FZ22	3000Ω averaging thermistor @ 77°F (25°C), Type II (blue leads)
ST-FZ24	10,000Ω averaging thermistor @ 77°F (25°C) Type II (yellow leads)
ST-FZ27	100,000Ω averaging thermistor @ 77°F (25°C), Type II (gray leads)
ST-FZ42	20,000Ω averaging thermistor @ 77°F (25°C), Type IV (green leads)
SENSING ELEMENT	
8	8' (2.44m) probe length, four elements total
12	12.5' (3.81m) probe length, four elements total
25	25' (7.62m) probe length, nine elements total
XW	Weather resistant housing option

ST-FZ3

25

Example: ST-FZ3-25 10,000Ω Type III averaging thermistor sensor with 25' (7.62m) probe and nine sensing elements

RELATED PRODUCTS

UR	Moisture resistant three-wire butt splice
M-648	Copper-plated capillary mounting end clip
M-633	Copper-plated capillary mounting mid-duct support
CC-1G	Plastic capillary mounting clip