



TEMPERATURE

STAINLESS STEEL SHEATH THERMISTOR AND RTD SENSORS

ST-R*S, ST-R*SC SERIES

DESCRIPTION

The Precon **Stainless Steel Sheath Sensors** provide precision remote temperature sensing for building automation systems and mechanical equipment room instrumentation. The active sensing element is a highly stable precision thermistor material or platinum RTD.

The sensing element is rugged and sealed with a thermally conductive compound in a versatile 3" (7.6 cm)-long stainless steel tube. The probe is waterproof, and the sensor is ideal for use in refrigeration cases or as a strap-on sensor for pipes.

ST-R*S

The **ST-R*S Stainless Steel Sheath Sensors** are suitable for direct application to pipe surfaces for chilled or hot water measurement. They are also used for freezer cases where moisture protection is important. These rugged strap-on sensors come with 8' (2.4m), 24-gauge zipcord leads.

ST-R*SC

The **ST-R*SC Stainless Steel Sheath Sensors** come with a rugged, 25' (7.6m) cable that allows for termination away from areas of condensation. It is an ideal choice for freezer case applications.

APPLICATION

Strap-on Applications: Where it is not practical to install immersion wells, the **Stainless Steel Sheath Sensors** may be strapped to the pipe. The **-C** option provides a 25' (7.6m) rugged cable that may be strapped on the outside of the pipe insulation. Pipe strap accessory (**APB-28**) provides a bracket under the insulation to hold the sensor securely in place.

Precon™



FEATURES

- **Lifetime warranty**
- **Wide selection of thermistor and RTD curves**
- **Tip sensitive for precise temperature response**
- **Durable 304 stainless steel casing**
- **Easy to mount to wall, box, or pipe**
- **Waterproof probe**
- **Ultra high accuracy optional**

SPECIFICATIONS

Accuracy

Thermistor $\pm 0.36^{\circ}\text{F}$ (0.2°C)

RTD

Type 63 $\pm 0.72^{\circ}\text{F}$ (0.40°C)

Type 71 $\pm 0.054^{\circ}\text{F}$ (0.03°C)

Type 81, 85 $\pm 0.27^{\circ}\text{F}$ (0.15°C)

Type 91 $\pm 0.54^{\circ}\text{F}$ (0.30°C)

Sensor types available

Thermistor 2.252 k Ω , 3 k Ω , 10 k Ω , 20 k Ω , 100 k Ω

RTD

Type 63 1000 Ω Nickel

Type 71, 81 100 Ω Pt 385 Curve

Type 85 1000 Ω Pt 385 Curve

Type 91 1000 Ω Pt 375 Curve

Temperature range

Thermistor 10° to 230°F (-12° to 110°C)

RTD

Type 63 -76° to 392°F (-60°C to 200°C)

Type 71 -58° to 572°F (-50°C to 300°C)

Type 81, 85, 91 -67° to 240°F (-55°C to 115°C)

Temperature response

Thermistor

Negative temperature coefficient

RTD

Positive temperature coefficient

Stability

Thermistor

0.24°F (0.13°C) over five years

RTD

<0.09°F (0.05°C) over five years

Heat dissipation

2.7 mW/°C (power needed to raise the temperature by 1°C)

Connections

8' (2.44m), 24 AWG zipcord using crimp or solder connection, type 71 & 81 have 18" leads

Mounting

Directly to wall or pipe using standard clips and brackets

Warranty

Lifetime

TEMPERATURE

STAINLESS STEEL SHEATH THERMISTOR AND RTD SENSORS

ST-R*S, ST-R*SC SERIES



TEMPERATURE


MOUNTING/WIRING

Mounting

Secure to wall or pipe using cable ties, clips, or brackets.

Wiring

Terminate with butt splices or solder connections. Wire nuts are not recommended.



When used as a strap-on sensor, best results are obtained when conductive compound (**TCC-12**) is applied between the sensor and the pipe. In addition, the sensor should be inserted under insulation with at least 2' (0.61m) on each side of the sensor. Adjustable pipe bracket **APB-28** is available for use with this sensor.

DIMENSIONS

in
(cm)

0.25
(0.64)

Polyolefin Sheath

3.0
(7.62)
Stainless Tube

ORDERING INFORMATION

MODEL	DESCRIPTION
ST-R3S	10,000Ω stainless steel thermistor @ 77°F (25°C), Type III (gray leads)
ST-R21S	2252Ω stainless steel thermistor @ 77°F (25°C), Type II (green leads)
ST-R22S	3000Ω stainless steel thermistor @ 77°F (25°C), Type II (blue leads)
ST-R24S	10,000Ω stainless steel thermistor @ 77°F (25°C), Type II (yellow leads)
ST-R27S	100,000Ω stainless steel thermistor @ 77°F (25°C), Type II (gray leads)
ST-R42S	20,000Ω stainless steel thermistor @ 77°F (25°C), Type IV (green leads)
ST-R63S	1000Ω nickel stainless steel RTD @ 70°F (21°C), (yellow leads)
ST-R71S	100Ω ultra high accurate stainless steel RTD @ 32°F (0°C), 385 platinum curve (blue leads)
ST-R81S	100Ω stainless steel RTD @ 32°F (0°C), 385 platinum curve (yellow leads)
ST-R85S	1000Ω stainless steel RTD @ 32°F (0°C), 385 platinum curve (blue leads)
ST-R91S	1000Ω stainless steel RTD @ 32°F (0°C), 375 platinum curve (green leads)

OPTIONS (List options in alphabetical order with dashes)

C	25' (7.6m) 22 AWG cable (not available with XZ option)
QD ¼	Nylon insulated Quick Disconnect ¼"
X25	25' (7.6m) lead length 24 AWG
XCP25	25' (7.6m) Non-shielded 22AWG plenum cable
XD	Dual sensors in one probe (Not with XC, XCP25)
XL	Custom length insertion probes 1" to 60"
XN	NIST Certificate of conformance
XN1	NIST certificate, one reference point 32°F(0°C)
XN2	NIST certificate, two reference points 32°F/158°F(0°C/70°C)
XN3	NIST certificate, three reference points 32°F/77°F/158°F(0°C/25°C/70°C)
XP	Matched sensor pair, matched to ±0.1°F, 0.05°C (must order two sensors)
XPA	Ultra high accuracy, thermistors only, ±0.135°F (0.075°C)
XZ	Three wire RTD connections (optional only on Type 81, standard on Type 71, not available with XC25 and XCP25)

ST-R3S

C

Example: **ST-R3S-C** 10,000Ω stainless steel sheath thermistor with 25' (7.6m) cable

RELATED PRODUCTS

UR	Moisture-resistant three-wire butt splice
APB-28	Adjustable pipe bracket 2" to 8" (5.1 to 20.3 cm)
TCC-12	Single application thermal conductive compound
TCC-111	Thermal conductive compound 111 ml tub
PN-46	Aluminum mounting clip
#20	Strap-on sensor self-vulcanizing stretch tape, 6' (1.83m) roll, 1" (2.54cm) wide