

TMIS-1

TURBINE MINI INTERCOM



FEATURES

- Background noise cancellation
- Built to last with robust die-cast aluminum frame
- Supports wide set of IP and networking standards
- White thermoplastic front plate with one button
- Ideal for Building Security and Public Environments

DESCRIPTION

All IP stations in the Vingtor-Stentofon Turbine series utilize the latest technology to create unparalleled audio quality. Some of the many features include: HD voice quality, Open Duplex, Active Noise Cancellation, MEMS microphone, and a Class D amplifier. These features, in conjunction with our 65+ years of experience with acoustic technology are only a few of the many factors that contribute to the superior audio quality of our products.

Turbine IP stations are compatible with the following systems:

- **SIP iPBX** – This station can be used with basically any SIP server. Various server types have been tested explicitly by STENTOFON and therefore a proper functionality can be confirmed. Check with your sales contact for the latest information on compatibility.
- **Vingtor-Stentofon Alphacom XE Audio servers** – CCoIP® (Critical Communication over IP). See www.vingtor-stentofon.com for more information.
- **Vingtor-Stentofon Pulse** – Intercom for everyone. See www.vingtor-stentofon.com for more information.



- ☒ **ALPHACOM XE**
- ☒ **PULSE**
- ☒ **SIP IPBX**



ITEM NUMBER	DESCRIPTION	SHIP WEIGHT
1008116010	TMIS-1 Turbine Mini Intercom	0.3 kg

TMIS-1 TURBINE MINI INTERCOM

SPECIFICATIONS

AUDIO

SPL rated power at 1m	90 dB
Noise cancelling - suppression of musical noise	YES
Noise cancelling - suppression of static noise	YES
Codecs	G.711, G.722, G.729
Frequency range, G.722 Codec	200 Hz – 7000 Hz
Audio technology	Modes: Full open duplex, switched open duplex Adaptive jitter filter Local tone generator Sound level detection (scream alarm) Automatic gain control (microphone)
Internal speaker amplifier	Class D
Microphone technology	Digital MEMS, omnidirectional microphone

HARDWARE

Ethernet connector	1 x RJ 45
All other connectors	Tool-less, spring loaded, vibration proof terminals
General inputs and outputs	6 (configurable)
Outputs	12mA as LED drivers
Change-over relay (NO+NC+COM)	Max: 250VAC/220VDC, 2A, 60W
Power options	PoE and or external power supply
PoE (Power over Ethernet)	IEEE 802.3af standard, Class 0 (0.44W to 12.95 W)
External power supply	24 VDC (16 – 48 V)
Power consumption	2.8 W
Audio line out / Induction loop signal	0 dBu / 600 Ohm
Button backlight	LED
Call indication	Icons/colors according to norm for hearing-impaired

CONSTRUCTION

Dimensions (HxVxD)	116 x 116 x 40 mm
Dimensions after flush mount	116 x 116 x 5 mm
Weight	0.3 kg
Faceplate material	3 mm / 0.12" PMMA, color-printed on back side
Base / Frame material	3 mm / 0.12" Aluminum alloy - A413.0, AlSi12Se, anodized and painted
Electronics cover material	Polycarbonate (translucent)
Button material	3 mm / 0.12" Polycarbonate (transparent)
Loudspeaker poke protection, large diameter objects	Thermoplastic faceplate with machined grille
Loudspeaker poke protection, small diameter objects	Stainless steel mesh, acoustically transparent

NETWORKING & PROTOCOLS

Protocols	IPv4 (with DiffServ), SIP, TCP, UDP, HTTPS, TFTP, RTP, DHCP, STENTOFON CCoIP®, NTP
LAN protocols	Power over Ethernet (IEEE 802.3 a-f) Network Access Control (IEEE 802.1x)
Management & Operation	HTTP/HTTPS (Web configuration) DHCP and static IP + STENTOFON Pulse™ Remote software upgrade Centralized monitoring
Advanced supervision functions	E.g. network test, tone test, status reports
SIP Support	RFC 3261 (SIP base standard) RFC 3515 (SIP refer) RFC 2976 (SIP info)
DTMF Support	RFC 2833, 2976 (SIP info)

ENVIRONMENT & COMPLIANCES

Ingress Protection rating	IP-42
Operating temperature range	-25° to 70° C / -13° to 158 ° F
Storage temperature range	-25° to 70° C / -13° to 158 ° F
Relative humidity	< 95% not condensing
UV-resistant	YES
EMC	EN 55022 Class B

OTHER SPECIFICATIONS

IP address information	Speaks IP address after system boot
Country of manufacture	Poland

